Data Sheet



Between Series Adaptor 33_QLA-BNC-01-1/1--_N

Description

Adaptor plug/jack
QLA-01 plug (male) / BNC jack (female)

Interface standards
Series QLA-01 - NIM-CAMAC-Standard CD/N549
Series BNC - IEC 61169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & \text{other } \Omega \\ \text{Interface frequency max.} & \text{1.4 GHz} \end{array}$

Mechanical Data

Number of matings 500
Weight 0.0085 kg

Environmental Data

Operating temperature -55 °C to 150 °C 2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

Material Data

Interface - QLA-01 plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing DCA-00014252

Ordering Information

Single package 33_QLA-BNC-01-1/1--_NE

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.