## **Crimp Terminals**

# multicomp PRO




#### **Specifications**


Terminal Material: Copper.Insulation Material: Vinyl.Max. Electrical Rating: 75°C 600 volts.

LBVE

Wire Range AWG	Max. Electric Current (Amperes)	Insulation Colour
22 to 16 (1.25mm <sup>2</sup> )	19	Red
16 to 14 (2mm <sup>2</sup> )	27	Blue
12 to 10 (5.5mm <sup>2</sup> )	48	Yellow

#### Diagram





### Specification Table

	Colour	W	L	С	В	Т	Е	Part Number
	Red	3	28	1.7	11.2	0.75	2.1	LBVE1-3
Γ	Blue		29.3	2.3	11.5	0.8		LBVE2-3
Γ	Red	1.9 2.8	23.2	1.7	11.2	0.75	-	PTVE1-12
Γ	Blue		23.5	2.3	11.5	0.8		PTVE2-12
Γ	Yellow		14	-	-	-		PTVE6-13

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farmell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

