
Data sheet | Item number: 890-243 Socket; 3-pole; Cod. B; 1,50 mm<sup>2</sup>; gray

www.wago.com/890-243







#### Item description

- Protected against mismating and maintenance-free
- Push-in CAGE CLAMP<sup>®</sup> spring pressure connection technology allows solid conductors to be simply pushed into a unit
- Compact design with 4.4 mm pole spacing
- Components can be clearly printed on and color-coded to meet custom requirements
- When assembled, the installation connectors complies with IP40 and are suitable for easily accessible areas

#### Note:

All connectors for mounted installations (snap-in versions for lighting fixtures or devices, all types of PCB and distribution connectors) are factoryequipped with locking levers to ensure plugs and sockets are securely locked. Additional locking levers are only required for flying leads (plug /socket).

#### Note on mismating protection:

All WINSTA<sup>®</sup> components are 100% protected against mismating when:

- a.) plugging different numbers of poles
- b.) plugging while rotated 180
- c.) plugging while laterally staggered
- d.) plugging one pole

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com



#### Safety information 1:

Application note for the U.S. market (USR): Some versions may also be used for current interruption in accordance with the UL certificate in select applications with currents below 5 A and voltages up to 600 V. For further information, please contact your local sales office.

# Data

### **Electrical data**

Note on Contact Resistance	approx. 1 m $\Omega$ of contact resistance approx. 0.25 m $\Omega$ contact
	transition plug/socket

#### Ratings per IEC/EN 60664-1

Ratings per	IEC/EN 60664-1
Nominal voltage (III/3)	250 V
Rated surge voltage (III/3)	4 kV
Rated current	16 A
Note on rated current	13 A for 3-pole load
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

# Approvals per UL 1977

Rated voltage UL 1977	600 V
Rated current UL 1977	14 A

#### **Connection data**

Operating tool
Push-in
1,5 mm²
0,25 1,5 mm² / 22 16 AWG
0,75 1,5 mm² / 20 16 AWG
0,25 1 mm² / 22 18 AWG
0,25 1,5 mm² / 22 16 AWG
0,25 0,75 mm² / 22 20 AWG
0,25 0,75 mm² / 22 20 AWG
0,75 mm² / 20 AWG
9 mm / 0.35 inch
see also packaging or instructions
3
3

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

www.wago.com/890-243



Total number of potentials	3
Conductor entry direction to mating direction	0°

# **Geometrical Data**

Pin spacing	4,4 mm / 0.173 inch
Width	15 mm / 0.591 inch
Height	11,7 mm / 0.461 inch
Depth	34,1 mm / 1.343 inch

#### Mechanical data

Coding	В
Mating force of a plug-in connection	approx. 20 70 N (depending on pole number)
Retention force of a plug-in connection	Locked: > 80 N
Unmating force of a plug-in connection	Unlocked: approx. 20 70 N (depending on pole number)
Number of mating cycles	200, without resistive load

100, with resistive load I $_{\rm N}$  = 16 A, tested (1.5 mm<sup>2</sup>/16 AWG)

Marking	123
Protection type	IP20
Note on protection type	IP40 with strain relief housing
Potential marking	123

# **Plug connection**

Contact type (pluggable connector)	Female connector/socket
Connector (connection type)	for conductor
Mismating protection	Yes
Locking of plug-in connection	locking lever
Locking lever	retrofittable

# Material Data

Color	gray
Insulation material	Polyamide 66 (PA 66)
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Copper or copper alloy (surface-treated)
Fire load	0.07 MJ

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

www.wago.com/890-243



Weight	3.6 g
Environmental Requirements	
Processing temperature	-5 +40 °C
Continuous operating temperature	-35 +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C
Commercial data	
Product Group	20 (WINSTA)
Packaging type	BOX

rackaging type	БОХ
Country of origin	PL
GTIN	4055143499910
Customs tariff number	85366990990

# Approvals / Certificates

# **Country specific Approvals**

Logo	Approval	Additional Approval Text	Certificate name
	CB DEKRA Certification B.V.	EN 61984	71-100413
KEUR			
	CCA	EN 60320	2148952.04
KEUR	DEKRA Certification B.V.		

#### Ship Approvals

Logo	Approval	Additional Approval Text	Certificate name
DNV-GL	DNV GL Det Norske Veritas, Germanischer Lloyd	-	TAE00001Z6
CIVORAN LA COMPANY	<b>LR</b> Lloyds Register	EN 61535	08/20047 (E2)
UL-Approvals			Certificate

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

# Data sheet | Item number: 890-243

www.wago.com/890-243



Logo	Approval	Additional Approval Text	name	
c <b>RN</b> us	cURus Underwriters Laboratories Inc.	UL 1977	E45171	
Counterpar	t			
Carl and	<b>Item no.890-1661</b> h-distribution connector; 3-pole; Cod. B; 1 input; 2 outputs; gray	www.wago.com/890-1661		
	Item no.890-1761 h-distribution connector; 3-pole; Cod. B; 1 input; 2 outputs; outputs on one side; 3 locking levers; for flying leads; gray		www.wago.com/890-1761	
No. No.	<b>Item no.890-853/011-000</b> Plug for PCBs; angled; 3-pole; Cod. B		www.wago.com/890-853/011- 000	
	<b>Item no.890-253</b> Plug; 3-pole; 1,50 mm²; gray		www.wago.com/890-253	
3  2  1	<b>Item no.890-853</b> Plug for PCBs; straight; 3-pole; Cod. B		www.wago.com/890-853	
	l <b>tem no.890-753</b> Snap-in plug; 3-pole; Cod. B; 1,50 mm²; gray		www.wago.com/890-753	
	Item no.891-8993/005-103 pre-assembled interconnecting cable; Eca; Socket/plug; 3- Item no.891-8993/205-103	pole; Cod. B; 1 m; 1,00 mm²; gray	www.wago.com/891-8993 /005-103 www.wago.com/891-8993	
	pre-assembled connecting cable; Eca; Plug/open-ended; 3	-pole; Cod. B; 1 m; 1,00 mm²; gray	/205-103	

# **Compatible products**

#### tools

**Item no.: 210-719** Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft

www.wago.com/210-719

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com


# Downloads CAD/CAE-Data

CAD data




2D/3D Models 890-243	URL	Download
CAE data		
EPLAN Data Portal 890-243	URL	Download
WSCAD Universe 890-243	URL	Download

# Handling Instructions



1. Strip length, outer insulation = 30 mm (2-pole), 37 mm (3-pole), 45 mm (4- and 5-pole)

To terminate fine-stranded conductors, open the clamping unit via screwdriver (2.5 mm blade width) and insert a stripped conductor until it hits backstop. Terminate solid conductors by simply pushing them in.



To terminate fine-stranded conductors, open clamping units via operating tool (890-382) and insert stripped conductors until they hit backstop.

Terminate solid conductors by simply pushing them in.

2. Strip length = 9 mm

3. Extended ground conductor = 8 mm


Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

# Data sheet | Item number: 890-243

www.wago.com/890-243





To terminate fine-stranded conductors, open clamping units via operating tool (890-383) and insert stripped conductors until they hit backstop.

Terminate solid conductors by simply pushing them in.

#### Installation



Latch wired connector onto the base of the strain relief housing.



Push down strain relief clamp by hand.



Push down strain relief clamp via 2.5 mm screwdriver alternately on both sides.

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

# Data sheet | Item number: 890-243 www.wago.com/890-243








Latch the top of the strain relief housing.

The printed marking of the connector is clearly visible in the openings of the strain relief housing.

#### **Mismating protection**



B-coded connectors with different colors can be plugged together.

B-coded connectors (shown in grav) not only

X4 Х3 ×2 R 8 Æ X8 X7 R E Æ H X12 X11 X10 χ9 Æ Æ Æ Æ

B-coded connectors (shown in gray) not only differ in color, but also in their design, making them incompatible with other coded connectors.

#### Important note:

Different colors and/or pole marking are used for circuit identification. Only connectors of the same color and same pole marking must be plugged together.

#### **Product family**

<i>WINSTA</i>® MINI special Show all products from the family

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com