


Technical data sheet

Ti2-SU1Z 608.8185.022 ΑН



Mechanical features

Enclosure: PBT, glass fibre reinforced

Cover: PA6.6, black

Actuator: Turret head, roller (thermoplast)

-30°C up to +80°C Ambient air temperature:

1 NC-contact, 1 NO-contact (Zb) Contact type:

3x10⁶ switch operations Mechanical life:

Switch frequency: max. 100/min

2xM4 or 2xM5 fixed positioning for safety applications Mounting:

Connection type: 4 screw connections (M3.5)

Conductor cross-section: single core 0.5-1.5mm² / litz wire with connector sleeve 0.5-1.5mm²

1 x M16x1.5 Cable entry size:

approx. 0,07kg Weight:

Electrical features

Max. voltage: 250 V AC I th 10A Max. enduring current:

Max. inrush current: according to IEC 947-5-1

Utilization categorie: AC 15,A300 240V/3A, 120V/6A / DC 13,Q300 250V/0.27A, 125V/0.55A

according to EN 60947-1; EN 60947-5-1 Standards:

IP65 according to EN 60529; DIN VDE 0470 T1 Protection class (IP-Code):

10A 300V AC, Ă300 CSA/UL:

Short circuit protection: Fuse 6A gL

Approach possibilities

By loosening the 4 screws the Actuation Assembly can be rotated in 90 degree increments such that 4 Actuation directions are possible. The Actuation Assembly is to be again fastened to the housing using the 4 screws.

Remarks

The moving parts should be oiled periodically.

The rated protection class (IP-Code) is valid only at closed cover and when using an at least equivalent cable gland.

Copies are not retreated in case of alternations