

Vishay

Wet Tantalum SMD HI-TMP[®] Capacitors for +200 °C Operation, Tantalum Metal Case With Glass-to-Tantalum Hermetic Seal



LINKS TO ADDITIONAL RESOURCES



PERFORMANCE CHARACTERISTICS

Operating Temperature: -55 °C to +85 °C (to +200 °C with voltage derating)

DC Leakage Current (DCL Max.): at +25 $^\circ C$ and above: leakage current shall not exceed the values listed in the Standard Ratings table.

Capacitance Tolerance: ± 10 %, ± 20 % standard

FEATURES

- Advanced SMD packaging with high volumetric efficiency, patents pending
- Enhanced performance, high reliability design
- SMD, 100 % tin (RoHS-compliant)
- Mounting: surface-mount
- Increased thermal shock capability of 300 cycles
- Designed for oil exploration, avionics, and aerospace applications where > 150 °C operation is required
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

ORDE	ORDERING INFORMATION						
T24	С	336	к	075	С	S	s
TYPE	CASE CODE See Standard Ratings table	CAPACITANCE This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow.	CAPACITANCE TOLERANCE K = ± 10 % M = ± 20 %	DC VOLTAGE RATING AT +85 °C I This is expressed in volts. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V).	$\begin{tabular}{ c c c c c c c c c c c c c c c c c c c$	RELIABILITY GRADE S = 48 h burn-in	ESR S = standard



Revision: 05-May-2020

(5-2008)



T24

Vishay



STANDARD RATINGS							
CAPACITANCE AT 25 °C	V _{DC} CASE		PART NUMBER	MAX. ESR 120 Hz	MAX. ESR MAX. DCL 120 Hz (μA)		LIFE TEST PERFORMANCE
μF)	AT 200 C			(Ω)	25 °C	85 °C / 125 °C	(h AT +200 °C)
			75 V _{DC} AT +8	85 °C			
33	45	С	T24C336(1)075(2)(3)(4)	2.5	1	5	2000
125 V _{DC} AT +85 °C							
10	75	С	T24C106(1)125(2)(3)(4)	5.5	1	5	2000

Note ٠

Part number definitions:

(1) Capacitance tolerance: K, M

(2) Termination and packaging: C, H, U
(3) Reliability level: S
(4) ESR: S

POWER DISSIPATION				
CASE CODE	MAXIMUM PERMISSIBLE POWER DISSIPATION AT +25 $^\circ$ C (W) IN FREE AIR			
С	0.9			

STANDARD PACKAGING QUANTITY			
CASE CODE		UNITS PER REEL	
CASE CODE	7" FULL REEL	7" HALF REEL	7" PARTIAL REEL
С	100	50	25



T24

Vishay



Notes

· Metric dimensions will govern. Dimensions in inches are rounded and for reference only.

- (1) A₀, B₀, K₀, are determined by the maximum dimensions to the ends of the terminals extending from the component body and / or the body dimensions of the component. The clearance between the ends of the terminals or body of the component to the sides and depth of the cavity (A₀, B₀, K₀) must be within 0.002" (0.05 mm) minimum and 0.020" (0.50 mm) maximum. The clearance allowed must also prevent rotation of the component within the cavity of not more than 20°.
- (2) Tape with components shall pass around radius "R" without damage. The minimum trailer length may require additional length to provide "R" minimum for 12 mm embossed tape for reels with hub diameters approaching N minimum.
- (3) This dimension is the flat area from the edge of the sprocket hole to either outward deformation of the carrier tape between the embossed cavities or to the edge of the cavity whichever is less.
- (4) This dimension is the flat area from the edge of the carrier tape opposite the sprocket holes to either the outward deformation of the carrier tape between the embossed cavity or to the edge of the cavity whichever is less.
- ⁽⁵⁾ The embossed hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location shall be applied independent of each other.
- ⁽⁶⁾ B₁ dimension is a reference dimension tape feeder clearance only.

CARRIER TAPE DIMENSIONS in inches [millimeters]					
TAPE WIDTH	W	P ₂	F	E ₁	E ₂ MIN.
16 mm	0.630 + 0.012 / - 0.004 [16.0 + 0.3 / - 0.1]	$\begin{array}{c} 0.079 \pm 0.004 \\ [2.0 \pm 0.1] \end{array}$	0.295 ± 0.004 [7.5 ± 0.1]	$\begin{array}{c} 0.069 \pm 0.004 \\ [1.75 \pm 0.1] \end{array}$	0.561 [14.25]



www.vishay.com

Vishay

CARRIER TAPE DIMENSIONS in inches [millimeters]					
ТҮРЕ	CASE CODE	TAPE WIDTH W (mm)	P ₁	K ₀ MAX.	B ₁ MAX.
T24	С	16	0.476 ± 0.004 [12.0 ± 0.1]	0.31 [7.9]	0.45 [11.3]

RECOMMENDED REFLOW PROFILES

Capacitors should withstand reflow profile as per J-STD-020 standard				
T _P Max. ramp-up rate = 3 °C/. Max. ramp-down rate = 6 °C/. T _s max. Preheat area T _s min. t_s T _s min. T _s min.	$T_{C/S}$ T_{C} - 5 °C			
PROFILE FEATURE	LEAD (Pb)-FREE ASSEMBLY			
Preheat / soak				
Temperature min. (T _{s min.})	150 °C			
Temperature max. (T _{s max.})	200 °C			
Time (t_s) from ($T_s _{min.}$ to $T_s _{max.}$)	60 s to 120 s			
Ramp-up				
Ramp-up rate (T _L to T _P)	3 °C/s max.			
Liquidus temperature (T _L)	217 °C			
Time (t_L) maintained above T_L	60 s to 150 s			
Peak package body temperature (T _p)	245			
Time (t_p) within 5 °C of the specified classification temperature (T_C)	30 s			
Time 25 °C to peak temperature	8 min max.			
Ramp-down				
Ramp-down rate (T _P to T _L)	6 °C/s max.			
Time 25 °C to peak temperature	8 min max.			



4

Vishay

TYPICAL PERFORMANCE CHARACTERISTICS OF T24 CAPACITORS

ELECTRICAL CHARACTERISTICS				
ITEM	PERFORMANCE CHARACTERISTICS			
Category temperature range	-55 °C to +85 °C (to +200 °C with voltage derating)			
Capacitance tolerance	± 20 %, ± 10 % at +25 °C, 120 Hz			
Capacitance change by temperature	Limit per Standard Ratings table			
ESR	Limit per Standard Ratings table, at +25 °C, 120 Hz			
Impedance	Limit per Standard Ratings table, at -55 °C, 120 Hz			
DCL (leakage current)	Limit per Standard Ratings table			
AC ripple current	Limit per Standard Ratings table, at +85 °C and 40 kHz			
Reverse voltage	Reverse voltage shall be in accordance with MIL-PRF-39006, paragraphs 3.23 and 4.8.19, except D potential will be maximum of 3 V			
Surge voltage	The DC surge voltage is the maximum voltage to which the capacitor can be subjected under any conditions including transients and peak ripple at the highest line voltage. The DC surge voltage is 115 % of rated DC voltage			



PERFORMANCE CHARACTERISTICS				
ITEM	CONDITION	POST TEST PERFORMANCE		
Surge voltage	In accordance with MIL-PRF-39006: 85 °C 1000 successive test cycles at the applicable DC surge voltage specified in series with a 1 k Ω resistor at the rate of 30 s ON, 5.5 min OFF	Capacitance change Leakage current	Within \pm 10 % of initial measured value Not to exceed specified value	
Life testing	In accordance with MIL-PRF-39006: capacitors shall be capable of withstanding life test at temperature +200 °C at derated voltage	Capacitance change Leakage current at 25 °C ESR	+10 % / -20 % of initial measured value Not to exceed specified value from "Standard Ratings" table Not to exceed 200 % of the applicable value from "Standard Ratings" table	
AC ripple life	In accordance with MIL-PRF-39006: 2000 h, +85 °C			

Revision: 05-May-2020

5



ENVIRONMENT	ENVIRONMENTAL CHARACTERISTICS				
ITEM	CONDITION	POST TEST PERFORMANCE			
Stability at low and high temperatures	As specified in MIL-PRF-39006	The capacitors shall m	neet the requirements of MIL-PRF-39006		
Seal	MIL-PRF-39006 Method 112 of MIL-STD-202, conditions A and C	When the capacitors a there shall be no evide	are tested as specified in MIL-PRF-39006, ence of leakage.		
Moisture resistance	MIL-PRF-55365 Method 106 of MIL-STD-202, number of cycles: 10 continuous cycles except that steps 7a and 7b shall be omitted.	DC leakage Capacitance change ESR	Not exceed 125 % of the specified value Within ± 10 % of the initial measured value Not exceed the specified value		
Barometric pressure (reduced)	Method 105 of MIL-STD-202, condition E (150 000 feet) (45,720.1 m).	There shall be no mec post-conditioning.	hanical or visual damage to capacitors		
Low temperature storage	MIL-PRF-39006 Method 502 of MIL-STD-810, Storage temperature: -62 °C + 0 °C, -3 °C Exposure time: 72 h followed by a 1 h exposure at +125 °C + 7 °C, -0 °C within 24 h after low temperature storage.	DC leakage Capacitance change ESR	Not to exceed 125 % of the specified value Within \pm 10 % of the initial measured value Not exceed the specified value		
Salt atmosphere (corrosion)	MIL-PRF-39006 Method 101 of MIL-STD-202, condition B (48 h), applicable salt solution: 5 %	There shall be no harn	nful corrosion. Marking shall remain legible.		

MECHANICAL PERFORMANCE CHARACTERISTICS				
CONDITION	POST TEST PERFORMANCE			
AEC-Q200-006 Apply a pressure load of 5 N for 10 s \pm 1 s horizontally to the center of capacitor side body.	DC leakage Capacitance change ESRNot to exceed 125 % of the specified value Within ± 10 % of the initial measured value Not exceed the specified valueThere shall be no mechanical or visual damage to capacitors post-conditioning.			
MIL-STD-202, method 208, test B ANSI/J-STD-002: Pb-free solder - test B1	All terminations shall exhibit a continuous solder coating free from defects for a minimum of 95 % of the critical area of any individual lead.			
MIL-STD-202, method 215	There shall be no mechanical or visual damage to capacitors post-conditioning. Marking shall remain legible, no degradation of the can material.			
Method 302 of MIL-STD-202, condition B (500 V_{DC} \pm 10 %)	The insulation resistance shall be not less than 100 M Ω . The capacitors shall meet the requirements of MIL-PRF-39006.			
MIL-STD-202, method 213,condition D (500 g)	The capacitors shall meet the requirements of MIL-PRF-39006.			
MIL-STD-202, method 204, condition H (80 <i>g</i> peak)	The capacitors shall meet the requirements of MIL-PRF-39006.			
MIL-STD-202, method 214, condition II-G (overall RMS 27.78 G)	The capacitors shall meet the requirements of MIL-PRF-39006.			
MIL-STD-202, method 107, condition A	Thermal shock shall be in accordance with MIL-PRF-39006 when tested for 300 cycles.			
MIL-STD-202, method 210, condition J, except with only one heat cycle	Capacitance change Within ± 10 % of initial ESR Initial specified value or less Leakage current Initial specified value or less There shall be no mechanical or visual damage to capacitors part of the specified value or less			
	PERFORMANCE CHARACTERISTICCONDITIONAEC-Q200-006Apply a pressure load of 5 N for 10 s \pm 1 s horizontally to the center of capacitor side body.MIL-STD-202, method 208, test B ANSI/J-STD-002: Pb-free solder - test B1MIL-STD-202, method 215Method 302 of MIL-STD-202, condition B (500 V _{DC} \pm 10 %)MIL-STD-202, method 213, condition D (500 g)MIL-STD-202, method 204, condition H (80 g peak)MIL-STD-202, method 214, condition II-G (overall RMS 27.78 G)MIL-STD-202, method 210, condition J, except with only one heat cycle			



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.