DATASHEET - M22-DDL-GR



Double actuator pushbutton, RMQ-Titan, Actuators and indicator lights non-flush, momentary, White lens, green, red, Blank, Bezel: titanium

Powering Business Worldwide*

6

Part no. M22-DDL-GR Catalog No. 216698 Alternate Catalog M22-DDL-GRQ

No.

EL-Nummer 4355672

(Norway)

Delivery program

Product range Basic function Single unit/Complete unit Design Description Button plate button plate Button plate Button plate button plate	Don'tory program	
Single unit/Complete unit Design Actuators and indicator lights non-flush momentary White lens Button plate B	Product range	RMQ-Titan
Description Button plate button plate Blank IP66 Front ring Connection to SmartWire-DT Bezel: titanium yes with SWD-RMQ connections	Basic function	Double actuators
momentary White lens Button plate button plate Blank Degree of Protection IP66 Front ring Bezel: titanium yes with SWD-RMQ connections	Single unit/Complete unit	Single unit
Description Button plate button plate Butt	Design	Actuators and indicator lights non-flush
Button plate button plate Button plate Button plate Button plate Blank Degree of Protection Front ring Connection to SmartWire-DT Breen, red Blank Blank Beacl: titanium yes with SWD-RMQ connections		momentary
button plate Button plate Button plate Button plate Blank Degree of Protection Front ring Connection to SmartWire-DT green, red Blank IP66 Bezel: titanium yes with SWD-RMQ connections	Description	White lens
Button plate Blank Degree of Protection Front ring Bezel: titanium Connection to SmartWire-DT Pessent SWD-RMQ connections	Button plate	
Blank Degree of Protection IP66 Front ring Connection to SmartWire-DT Bezel: titanium yes with SWD-RMQ connections	button plate	green, red
Degree of Protection IP66 Front ring Bezel: titanium Connection to SmartWire-DT yes with SWD-RMQ connections	Button plate	
Front ring Connection to SmartWire-DT Bezel: titanium yes with SWD-RMQ connections		
Connection to SmartWire-DT yes with SWD-RMQ connections		
with SWD-RMQ connections	Front ring	Bezel: titanium
Front dimensions 29,7 x 54,7	Connection to SmartWire-DT	
	Front dimensions	29,7 x 54,7

Technical data

Genera

General			
Standards			IEC/EN 60947 VDE 0660
Lifespan, mechanical	Operations	x 10 ⁶	> 0.2
Operating frequency	Operations/h		≦ 3600
Actuating force		n	≦5
Climatic proofing			Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Degree of Protection			IP66
Ambient temperature			
Open		°C	-25 - +70
Storage		°C	- 40 - + 80
Mounting position			As required
Mechanical shock resistance		g	30 Shock duration 11 ms Sinusoidal according to IEC 60068-2-27
shipping classification			DNV GL LR







Indoor and protected outdoor installation

Design verification as per IEC/EN 61439

In	Α	0
P _{vid}	W	0
P _{vid}	W	0
P _{vs}	W	0
P _{diss}	W	0
	°C	-25
	°C	70
		Meets the product standard's requirements.
		Meets the product standard's requirements.
		Meets the product standard's requirements.
nt		Meets the product standard's requirements.
		Please enquire
		Does not apply, since the entire switchgear needs to be evaluated.
		Does not apply, since the entire switchgear needs to be evaluated.
		Meets the product standard's requirements.
		Does not apply, since the entire switchgear needs to be evaluated.
		Meets the product standard's requirements.
		Does not apply, since the entire switchgear needs to be evaluated.
		Does not apply, since the entire switchgear needs to be evaluated.
		Is the panel builder's responsibility.
		Is the panel builder's responsibility.
		Is the panel builder's responsibility.
		Is the panel builder's responsibility.
		Is the panel builder's responsibility.
		Not applicable.
		Is the panel builder's responsibility. The specifications for the switchgear must b observed.
		Is the panel builder's responsibility. The specifications for the switchgear must b observed.
		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
	P_{vid} P_{vid} P_{vs}	P _{vid} W P _{vid} W P _{vid} W P _{vs} W P _{diss} W °C °C

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Front element for push button (EC000221)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Front element for push-button actuators (ecl@ss10.0.1-27-37-12-10 [AKF028014])


(ecl@ss10.0.1-27-37-12-10 [AKF028014])		
Colour button		Other
Number of command positions		2
Construction type lens		Round
Hole diameter	mm	22.5
Width opening	mm	0


Height opening	mm	0
Type of button		Flat
Suitable for illumination		Yes
With protective cover		No
Labelled		No
Switching function latching		No
Spring-return		Yes
With front ring		Yes
Material front ring		Plastic
Colour front ring		Chrome
Degree of protection (IP), front side		IP66
Degree of protection (NEMA), front side		4X

Approvals

Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	012528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified
Degree of Protection	UL/CSA Type 3R, 4X, 12, 13

Dimensions





Additional product information (links)

IL04716002Z (AWA1160-1745) RMQ-Titan System

IL04716002Z (AWA1160-1745) RMQ-Titan System ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL04716002Z2018_10.pdf