



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 11

SDS No. : 618082  
V001.0

BERGQUIST SIL PAD TSP Q2000 known as Q-Pad 3

Revision: 30.11.2018  
printing date: 16.06.2020  
Replaces version from: -

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

BERGQUIST SIL PAD TSP Q2000 known as Q-Pad 3

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Thermal Interface Material

#### 1.3. Details of the supplier of the safety data sheet

Henkel AG & Co. KGaA

Henkelstr. 67

40589 Düsseldorf

Germany

Phone: +49 211 797 0

Fax-no.: +49 211 798 2009

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

#### 2.2. Label elements

##### Label elements (CLP):

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

#### 2.3. Other hazards

None if used properly.

This article contains components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB).

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

##### General chemical description:

Manufactured item - article

##### Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Octamethylcyclotetrasiloxane 556-67-2	209-136-7 01-2119529238-36	>= 0,3- < 2,5 %	Flam. Liq. 3 H226 Repr. 2 H361f Aquatic Chronic 4 H413 ===== EU. REACH Candidate List of Substances of Very High Concern for Authorization (SVHC)

For full text of the H - statements and other abbreviations see section 16 "Other information".  
Substances without classification may have community workplace exposure limits available.

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

##### Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

##### Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

##### Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

##### Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

#### 4.2. Most important symptoms and effects, both acute and delayed

No data available.

#### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

##### Suitable extinguishing media:

water, carbon dioxide, foam, powder

##### Extinguishing media which must not be used for safety reasons:

High pressure waterjet

#### 5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO<sub>2</sub>) and nitrogen oxides (NO<sub>x</sub>) can be released.

In case of fire, keep containers cool with water spray.

#### 5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

**Additional information:**

In case of fire, keep containers cool with water spray.

**SECTION 6: Accidental release measures****6.1. Personal precautions, protective equipment and emergency procedures**

Avoid contact with skin and eyes.

Wear protective equipment.

Ensure adequate ventilation.

**6.2. Environmental precautions**

Do not empty into drains / surface water / ground water.

**6.3. Methods and material for containment and cleaning up**

Scrape up as much material as possible.

Sweep up spilled material. Avoid creating dust.

Keep in suitable and closed containers for disposal.

**6.4. Reference to other sections**

See advice in section 8

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

Avoid skin and eye contact.

See advice in section 8

Hygiene measures:

Good industrial hygiene practices should be observed.

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

**7.2. Conditions for safe storage, including any incompatibilities**

Ensure good ventilation/extraction.

Keep container tightly sealed.

Refer to Technical Data Sheet

**7.3. Specific end use(s)**

Thermal Interface Material

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational Exposure Limits

Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Graphite 7782-42-5 [GRAPHITE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Graphite 7782-42-5 [GRAPHITE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Graphite 7782-42-5 [DUST, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Graphite 7782-42-5 [DUST, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 7631-86-9 [SILICA, AMORPHOUS, INHALABLE DUST]		6	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 7631-86-9 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		EH40 WEL

#### Occupational Exposure Limits

Valid for  
Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Graphite 7782-42-5 [GRAPHITE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Graphite 7782-42-5 [GRAPHITE, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL
Graphite 7782-42-5 [DUSTS, NON-SPECIFIC, RESPIRABLE]		4	Time Weighted Average (TWA):		IR_OEL
Graphite 7782-42-5 [DUSTS, NON-SPECIFIC, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 7631-86-9 [SILICA, AMORPHOUS, TOTAL INHALABLE DUST]		6	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 7631-86-9 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		IR_OEL

**Predicted No-Effect Concentration (PNEC):**

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Octamethylcyclotetrasiloxane 556-67-2	aqua (freshwater)		0,0015 mg/l				
Octamethylcyclotetrasiloxane 556-67-2	aqua (marine water)		0,00015 mg/l				
Octamethylcyclotetrasiloxane 556-67-2	sewage treatment plant (STP)		10 mg/l				
Octamethylcyclotetrasiloxane 556-67-2	sediment (freshwater)				3 mg/kg		
Octamethylcyclotetrasiloxane 556-67-2	sediment (marine water)				0,3 mg/kg		
Octamethylcyclotetrasiloxane 556-67-2	oral				41 mg/kg		
Octamethylcyclotetrasiloxane 556-67-2	Soil				0,54 mg/kg		

**Derived No-Effect Level (DNEL):**

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Octamethylcyclotetrasiloxane 556-67-2	Workers	inhalation	Long term exposure - systemic effects		73 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	Workers	inhalation	Long term exposure - local effects		73 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	Workers	inhalation	Acute/short term exposure - systemic effects		73 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	Workers	inhalation	Acute/short term exposure - local effects		73 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	General population	inhalation	Long term exposure - systemic effects		13 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	General population	inhalation	Long term exposure - local effects		13 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	General population	inhalation	Acute/short term exposure - systemic effects		13 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	General population	inhalation	Acute/short term exposure - local effects		13 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	General population	oral	Long term exposure - systemic effects		3,7 mg/kg	
Octamethylcyclotetrasiloxane 556-67-2	General population	oral	Acute/short term exposure - systemic effects		3,7 mg/kg	

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**

Engineering controls:

Ensure good ventilation/extraction.

**Respiratory protection:**

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

**Hand protection:**

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Wear protective glasses.

Protective eye equipment should conform to EN166.

**Skin protection:**

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

**Advices to personal protection equipment:**

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

## SECTION 9: Physical and chemical properties

**9.1. Information on basic physical and chemical properties**

Appearance	solid solid black
Odor	Slight
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	Product is a solid.
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density	No data available / Not applicable
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative)	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**9.2. Other information**

No data available / Not applicable

**SECTION 10: Stability and reactivity****10.1. Reactivity**

None.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**

Stable under normal conditions of storage and use.

**10.5. Incompatible materials**

See section reactivity.

**10.6. Hazardous decomposition products**

carbon oxides.

**SECTION 11: Toxicological information****11.1. Information on toxicological effects****Acute oral toxicity:**

Hazardous substances CAS-No.	Value type	Value	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	LD50	> 4.800 mg/kg	rat	equivalent or similar to OECD Guideline 401 (Acute Oral Toxicity)

**Acute dermal toxicity:**

Hazardous substances CAS-No.	Value type	Value	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	LD50	2.375 mg/kg	rat	equivalent or similar to OECD Guideline 402 (Acute Dermal Toxicity)

**Acute inhalative toxicity:**

Hazardous substances CAS-No.	Value type	Value	Test atmosphere	Exposure time	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	LC50	36 mg/l	dust/mist	4 h	rat	OECD Guideline 403 (Acute Inhalation Toxicity)

**Skin corrosion/irritation:**

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	not irritating		rabbit	equivalent or similar to OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

**Serious eye damage/irritation:**

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	not irritating		rabbit	equivalent or similar to OECD Guideline 405 (Acute Eye Irritation / Corrosion)

**Respiratory or skin sensitization:**

Hazardous substances CAS-No.	Result	Test type	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)

**Germ cell mutagenicity:**

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	negative	bacterial gene mutation assay	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Octamethylcyclotetrasiloxane 556-67-2	negative	in vitro mammalian chromosome aberration test	with and without		equivalent or similar to OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Octamethylcyclotetrasiloxane 556-67-2	negative	mammalian cell gene mutation assay	with and without		equivalent or similar to OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
Octamethylcyclotetrasiloxane 556-67-2	negative	inhalation		rat	equivalent or similar to OECD Guideline 475 (Mammalian Bone Marrow Chromosome Aberration Test)
Octamethylcyclotetrasiloxane 556-67-2	negative	oral: gavage		rat	equivalent or similar to OECD Guideline 478 (Genetic Toxicology: Rodent Dominant Lethal Test)

**Carcinogenicity**

No data available.

**Reproductive toxicity:**

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	NOAEL P 300 ppm NOAEL F1 300 ppm	two-generation study	inhalation	rat	equivalent or similar to OECD Guideline 416 (Two-Generation Reproduction Toxicity Study)

**STOT-single exposure:**

No data available.

**STOT-repeated exposure::**

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	LOAEL 35 ppm	inhalation	6 h nose only inhalation 5 days/week for 13 weeks	rat	OECD Guideline 412 (Repeated Dose Inhalation Toxicity: 28/14-Day)
Octamethylcyclotetrasiloxane 556-67-2	NOAEL 960 mg/kg	dermal	3 w 5 d/w	rabbit	equivalent or similar to OECD Guideline 410 (Repeated Dose Dermal Toxicity: 21/28-Day Study)

**Aspiration hazard:**

No data available.



## SECTION 12: Ecological information

### 12.1. Toxicity

#### Toxicity (Fish):

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	NOEC	0,0044 mg/l	93 d	Salmo gairdneri (new name: Oncorhynchus mykiss)	other guideline:
Octamethylcyclotetrasiloxane 556-67-2	LC50		96 h	Oncorhynchus mykiss	EPA OTS 797.1400 (Fish Acute Toxicity Test)

#### Toxicity (Daphnia):

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	EC50		48 h	Daphnia magna	EPA OTS 797.1300 (Aquatic Invertebrate Acute Toxicity Test, Freshwater Daphnids)

#### Chronic toxicity to aquatic invertebrates

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	NOEC	7.9 µg/l	21 d	Daphnia magna	EPA OTS 797.1330 (Daphnid Chronic Toxicity Test)

#### Toxicity (Algae):

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	EC50		96 h	Selenastrum capricornutum (new name: Pseudokirchneriella subcapitata)	EPA OTS 797.1050 (Algal Toxicity, Tiers I and II)
Octamethylcyclotetrasiloxane 556-67-2	NOEC	< 0,022 mg/l	96 h	Selenastrum capricornutum (new name: Pseudokirchneriella subcapitata)	EPA OTS 797.1050 (Algal Toxicity, Tiers I and II)

#### Toxicity to microorganisms

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	EC50		3 h	activated sludge	ISO 8192 (Test for Inhibition of Oxygen Consumption by Activated Sludge)

### 12.2. Persistence and degradability

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
Octamethylcyclotetrasiloxane 556-67-2	not readily biodegradable.	aerobic	3,7 %	29 d	OECD Guideline 310 (Ready BiodegradabilityCO <sub>2</sub> in Sealed Vessels (Headspace Test)

### 12.3. Bioaccumulative potential

Hazardous substances CAS-No.	Bioconcentratio n factor (BCF)	Exposure time	Temperature	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	12.400	28 d		Pimephales promelas	EPA OTS 797.1520 (Fish Bioconcentration Test-Rainbow Trout)

### 12.4. Mobility in soil

Hazardous substances CAS-No.	LogPow	Temperature	Method
Octamethylcyclotetrasiloxane 556-67-2	6,488	25,1 °C	OECD Guideline 123 (Partition Coefficient (1-Octanol / Water), Slow-Stirring Method)

#### 12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
Octamethylcyclotetrasiloxane 556-67-2	Fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

#### 12.6. Other adverse effects

No data available.

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

Product disposal:

Do not empty into drains / surface water / ground water.

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

Dispose of in accordance with local and national regulations.

### SECTION 14: Transport information

#### 14.1. UN number

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content  
(2010/75/EC) 0 %

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

**SECTION 16: Other information**

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H226 Flammable liquid and vapor.

H361f Suspected of damaging fertility.

H413 May cause long lasting harmful effects to aquatic life.

**Further information:**

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**