### DATASHEET - NZM1-XU24DC



Undervoltage release, 24 V DC

Part no. Catalog No.

NZM1-XU24DC 259452

0004315547

EL-Nummer (Norway)



#### **Delivery program**

| Product range         |    |   | Accessories  |
|-----------------------|----|---|--|
| Accessories           |    |   | Undervoltage release   |
| Accessories           |    |   | Undervoltage releases  |
| Standard/Approval     |    |   | UL/CSA, IEC  |
| Construction size     |    |   | NZM1   |
| Description           |    |   | Non-delayed disconnection of NZM circuit-breaker or N switch-disconnector<br>when the control voltage sinks below 35 – 70% U <sub>S</sub> .<br>For use with emergency-stop devices in connection with an emergency-stop<br>button.<br>When the under-voltage trip is switched off, accidental contact with the circuit<br>breaker's primary contacts is prevented when switched on.<br>Undervoltage releases cannot be installed simultaneously with NZMXHIV<br>early-make auxiliary contact or NZMXA shunt release. |
| Connection type       |    |   | with terminal block on the left-hand switch side   |
| Auxiliary contacts    |    |   | without auxiliary contact  |
| Rated control voltage | Us | V | 24 V DC  |
| For use with          |    |   | NZM1(-4), N(S)1(-4)  |

#### **Technical data**

#### **Undervoltage release** Rated control voltage $U_{\rm s}$ ٧ DC Us V DC 24 - 24 Rated control voltage Us ٧ 24 V DC Operating range Drop-out voltage x U<sub>s</sub> 0.35 - 0.7 Pick-up voltage x Uc 0.85 - 1.1 Power consumption AC Pick-up AC VA 1.5 Sealing AC VA 1.5 DC x U<sub>s</sub> Pick-up DC W 0.8 Sealing DC W 0.8 Maximum opening delay (response time until opening of the main contacts) 19 ms Minimum command time 10 - 15 ms **Terminal capacities** 1 x (0,75 - 2,5) 2 x (0,75 - 2,5) Solid or flexible conductor, with ferrule mm<sup>2</sup> AWG 1 x (18 ... 14)

# Design verification as per IEC/EN 61439

| IEC/EN 61439 design verification  |  |
|---|--|
| 10.2 Strength of materials and parts  |  |
| 10.2.2 Corrosion resistance   | Meets the product standard's requirements. |
| 10.2.3.1 Verification of thermal stability of enclosures  | Meets the product standard's requirements. |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat  | Meets the product standard's requirements. |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat<br>and fire due to internal electric effects | Meets the product standard's requirements. |

2 x (18 ... 14)



| 10.2.4 Resistance to ultra-violet (UV) radiation         | Meets the product standard's requirements.   |
|--|--|
| 10.2.5 Lifting   | Does not apply, since the entire switchgear needs to be evaluated.   |
| Ũ  |  |
| 10.2.6 Mechanical impact                                 | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.2.7 Inscriptions                                      | Meets the product standard's requirements.   |
| 10.3 Degree of protection of ASSEMBLIES                  | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.4 Clearances and creepage distances                   | Meets the product standard's requirements.   |
| 10.5 Protection against electric shock                   | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.6 Incorporation of switching devices and components   | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.7 Internal electrical circuits and connections        | Is the panel builder's responsibility.   |
| 10.8 Connections for external conductors                 | Is the panel builder's responsibility.   |
| 10.9 Insulation properties                               |  |
| 10.9.2 Power-frequency electric strength                 | Is the panel builder's responsibility.   |
| 10.9.3 Impulse withstand voltage                         | Is the panel builder's responsibility.   |
| 10.9.4 Testing of enclosures made of insulating material | Is the panel builder's responsibility.   |
| 10.10 Temperature rise                                   | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating                               | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.12 Electromagnetic compatibility                      | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.13 Mechanical function                                | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |

## **Technical data ETIM 7.0**

Low-voltage industrial components (EG000017) / Under voltage coil (EC001022)


Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Undervoltage trip (ecl@ss10.0.1-27-37-04-17 [AKF015013])

| Rated control supply voltage Us at AC 50HZ    | V | 0 - 0            |
|---|---|------------------|
| Rated control supply voltage Us at AC 60HZ    | V | 0 - 0            |
| Rated control supply voltage Us at DC         | V | 24 - 24          |
| Voltage type for actuating                    |   | DC               |
| Type of electric connection                   |   | Screw connection |
| Number of contacts as normally open contact   |   | 0                |
| Number of contacts as normally closed contact |   | 0                |
| Number of contacts as change-over contact     |   | 0                |
| Delayed                                       |   | No               |
| Suitable for power circuit breaker            |   | Yes              |
| Suitable for off-load switch                  |   | Yes              |
| Suitable for motor safety switch              |   | No               |
| Suitable for overload relay                   |   | No               |

#### **Approvals**

| Product Standards           | UL489; CSA-C22.2 No. 5-09; IEC60947, CE marking |
|-----------------------------|---|
| UL File No.                 | E140305   |
| UL Category Control No.     | DIHS  |
| CSA File No.                | 022086  |
| CSA Class No.               | 1437-01   |
| North America Certification | UL listed, CSA certified                        |

### **Dimensions**



2 NZM1-XA(HIV)(L) NZM1-XU(V)(HIV)(L)(20) NZM1-XHIV(L) ③ NZM1-XHIVR

#### Additional product information (links)

#### IL01203002Z (AWA1230-1914) Shunt release, Undervoltage release, Early-make auxiliary contact

IL01203002Z (AWA1230-1914) Shunt release, Undervoltage release, Early-make auxiliary contact

ftp://ftp.moeller.net/DOCUMENTATION/AWA\_INSTRUCTIONS/IL01203002Z2010\_11.pdf