

## Lowest Profile 4 Mbits/s (FIR) Infrared Transceiver Module

### Description


The Vishay TFBS6614 is the lowest profile (2.7 mm) 4 Mbit/s Infrared Data Transceiver module available. A PIN photodiode, an infrared emitter (IRED) and a low-power CMOS control IC are integrated in a single package that provides a total front-end solution.

$V_{\text{LOGIC}}$  - allows a low-voltage controller to connect directly to TxD, RxD and SD/Mode logic signals of the transceiver hence eliminating the need for costly signal level converter and reducing power consumption. The TxD-echo function is enabled for internal self-test. During transmission the TxD signals are echoed at RxD output to perform the internal self-test.

The Shut Down (SD) feature cuts current consumption to less than 10 nA.

### Features

- Smallest FIR Transceiver available:  
H 2.7 mm x W 3.33 mm x L 7.98 mm
- 1.0 m Link distance
- Battery & Power Management Features:
  - > Receive - 2 mA Typical
  - > Shutdown - 10 nA Typical
  - > Independent LED Anode Power Supply
  - > Wide Voltage Range 2.7 V - 5.5 V
  - > Power Up Latency < 100  $\mu$ s
  - > High  $V_{\text{CC}}$  Noise Rejection > 100 m VPP
- The TxD-Echo function is enabled
- $V_{\text{LOGIC}}$  (1.5 V - 5.5 V) - Independent Digital supply voltage
- Shutdown Tri-States Receiver Output and Disables TxD allowing Bus Interfacing
- High Immunity to Fluorescent Light Noise and AC Field. No external shield required
- High DC Ambient Rejection - Operates Outdoors
- Receiver Latency Less than 100  $\mu$ s
- Directly Interfaces with Various Super I/O and Controller Devices




### Applications

PDA's  
Mobile Phones  
Notebook Computers, Desktop PCs  
Digital Still and Video Cameras  
External Infrared Adapters (Dongles)  
Diagnostics Systems  
Medical and Industrial Data Collection Devices  
GPS

## Parts Table


Part	Description	Qty / Reel
TFBS6614-TR3	Oriented in carrier tape for side view surface mounting	2500 pcs

## Functional Block Diagram



## Pinout

TFBS6614  
weight 80 mg



## Absolute Maximum Ratings

Reference Point Ground, Pin 8, unless otherwise noted

Parameter	Test Conditions	Symbol	Min	Typ.	Max	Unit
Analog Supply Voltage Range, all states		$V_{CC1}$	- 0.5		+ 6.0	V
Digital Supply Voltage Range		$V_{DD}$	- 0.5		+ 6.0	V
Input Current	During Transmit, $V_{CC} = 5.0$ V, $TxD = V_{DD}$				10.0	mA
Output Sink Current, RxD					25.0	mA
Peak IRED Current	$V_{CC1} = 2.7$ V, $TxD = V_{DD}$ , 125 ns pulse				650	mA
Average IRED Current	$V_{CC2} = 2.7$ V				125	mA
Power Dissipation					500	mW
Junction Temperature					125	°C
Ambient Temperature Range (Operating)		$T_A$	- 25		+ 85	°C
Storage Temperature Range		$T_S$	- 25		+ 85	°C
Soldering Temperature	$t = 20$ s @ 215 °C			215	240	°C
Transmitter Data and Shutdown Input Voltage		$V_{TxD}, V_{SD}$	- 0.5		$V_{DD} + 0.5$	V
Receiver Data Output Voltage		RxD	- 0.5		$V_{DD} + 0.5$	V

## Optoelectronic Characteristics

### Receiver

 $T_A = 25$  °C,  $V_{CC} = 2.7$  V to 5.5 V unless otherwise noted

Parameter	Test Conditions	Symbol	Min	Typ.	Max	Unit
Minimum Detection Threshold Irradiance	4.0 Mbit/s, $\lambda = 850$ nm to 900 nm	$E_e$			100	mW/m <sup>2</sup>
Analog Supply Voltage Range	Specified operation	$V_{CC}$	2.7		5.5	V
Digital Supply Voltage Range	Specified operation	$V_{DD}$	1.5		5.5	V
Maximum LED Anode Voltage		$V_{LEDA}$			$V_{CC} + 4$	V
$I_{CC}$ Shut Down Current	$V_{CC} = 5$ V	$I_{CC1}$		0.01	2.0	μA
$I_{CC}$ Idle Current	$V_{CC} = 5$ V	$I_{CC2}$		1.6		mA

### Transmitter

 $T_A = 25$  °C,  $V_{CC} = 2.7$  V to 5.5 V unless otherwise noted

Parameter	Test Conditions	Symbol	Min	Typ.	Max	Unit
Output Radiant Intensity	$\alpha = 0$ °C, 15 °C, $TxD = \text{High}$ , $SD = \text{Low}$	$I_e$		110		mW/sr

## Mode Switching

Upon power-up the TFBS6614 module initializes in the SIR (9.6 kbit/s to 115.2 kbit/s) mode. The module can be switched to higher bandwidth and vice versa by using the sequence described below:




Figure 1. Mode Switching Timing Diagram

## Setting to the High Bandwidth Mode (0.576 Mbit/s to 4 Mbit/s)


1. Set SD/ Mode input to logic "High".

2. Set TxD input to logic "High". Wait  $t_s \geq 200$  ns.
3. Set SD/ Mode to logic "Low" (the negative edge latches state of TxD, which determines data rate setting).
4. After waiting  $t_h \geq 200$  ns TxD can be set to logic "Low". The hold time of TxD is limited by the maximum allowed pulse width. TxD is now enabled as normal TxD input for the high bandwidth mode.

## Setting to the Lower Bandwidth Mode (9.6 kbit/s to 115.2 kbit/s)


1. Set SD/ Mode input to logic "High".
2. Set TxD input to logic "Low". Wait  $t_s \geq 200$  ns.
3. Set SD/ Mode to logic "Low" (the negative edge latches state of TxD, which determines data rate setting).
4. After waiting  $t_h \geq 200$  ns TxD can be set to logic "Low". The hold time of TxD is limited by the maximum allowed pulse width. TxD is now enabled as normal TxD input for the lower bandwidth mode.

## Recommended Solder Profile




## Recommended Circuits



Circuit Diagram with separate  $V_{CC}$  and  $V_{LOGIC}$   
(I/O voltage follows  $V_{DD}$  voltage swing)



Circuit Diagram with a Common Power Supply for  $V_{CC}$  and  $V_{LOGIC}$   
(I/O voltage follows  $V_{CC}$  voltage swing)





## Package Dimensions in mm




technical drawings according to DIN specifications

All dimensions in mm  
Tolerances  $\pm 0.2$



### Recommended PCB Footprint




\* min 0.2 Photoimageable solder mask recommended between pads to prevent bridging

Drawing-No.: 6.550-5258.01-4

Issue: 1; 24.06.03

18074

## Reel Dimensions



14017


Tape Width	A max.	N	$W_1$ min.	$W_2$ max.	$W_3$ min.	$W_3$ max.
mm	mm	mm	mm	mm	mm	mm
24	330	60	24.4	30.4	23.9	27.4

# TFBS6614

Vishay Semiconductors



Tape Dimensions in mm



18297



## **Ozone Depleting Substances Policy Statement**

It is the policy of **Vishay Semiconductor GmbH** to

1. Meet all present and future national and international statutory requirements.
2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

**Vishay Semiconductor GmbH** has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

**Vishay Semiconductor GmbH** can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

### **We reserve the right to make changes to improve technical design and may do so without further notice.**

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany  
Telephone: 49 (0)7131 67 2831, Fax number: 49 (0)7131 67 2423