



SPECIFICATION SHEET

Product Code

PA130100BK

Product Description

 Rewireable C13 IEC Lock+ LSZH
Appliance Outlet (Black)


- Rewireable
- Fits any standard C14 outlet
- Anti-Vibrate
- Integral plug retention feature
- Easy pull handle
- Slotted and Cross head housing screws
- Appliance inlet suitable for cold conditions

General Information

Rated Current / Voltage	10A/250V~
Number Of Poles	2 + Earth (2 + PE)
Materials	Outer Body: Nylon (PA66) LSZH (RAL 9004 Signal Black)
	Housing Lid: Nylon (PA66) LSZH (RAL 9004 Signal Black)
	Chassis & Chassis Lid: Nylon (PA66) LSZH (RAL 9004 Signal Black)
	Cable Restraint: Nylon (PA66)
	Housing Screws & Cable Restraint Screws: Steel
	Lock Pivot Lever: Polycarbonate
	Terminal Block & Sliding Terminal: Brass
	Terminal Screws: Steel Brass Coated
	Spring: Spring Steel
	Locking Blade: Hardened Steel Zinc Plated
	Red Handle: Polycarbonate LSZH (RAL 3020 Traffic Light Red)
	Terminal Capacity
Torque Value	Terminal Screws; 0.4Nm, Strain Relief Clamping Screws; 0.3Nm
Operational Temperature	-20°C To +55°C
Dielectric Strength	1.5 kV Max
Withdrawal Force	>100N
Flammability Rating	Equivalent to UL94V-0
Protection Class	Suitable for appliances with protection Class I according to IEC EN 61140
Wire Stripping Lengths	Live & Neutral: 18mm
	Earth: 23mm

Standards & Approvals

KEMA-KEUR Certified: 2186208.01 - EN 60320-1:2001+A1:2007

UL File: E475619 - UL 60320-1 / CSA C22.2 No. 60320-1

SAA Certified: SAA-151920-EA - AS/NZS 60320.1.2012





SPECIFICATION SHEET

