

LED PIPE High OUTPUT

LED PIPE G2 L900 HIGH OUTPUT NW

0051048



Product features

- LED T5 replacement batten, high output range: more lumens per meter with efficiency up to 125 lum/watt, seamless linking (up to 10M), Ideal for direct lighting such as under cabinet or in kitchens, 150 degree beam angle, includes switch, includes 0.30m stripped cable, white polycarbonate body, includes standard and tilting brackets



PRODUCT OVERVIEW

IPC Code	0051048
Product name	LED PIPE G2 L900 HIGH OUTPUT NW
Technology	LED
Housing	PC Polycarbonate
General application	Residential & Consumer,
Certifications	EUNEW009
ETIM Class	EC000109
E-number SE	7505155
Fixture luminous flux (lm)	1500
Luminaire efficacy (lm/W)	115
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Photobiological Risk Group	RG0
Total power consumption (W)	13
Electrical protection	Class II
Dimmable	N
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5410288510484
Lamps	Yes

DATA TABLE

General data

IPC Code	0051048
Product name	LED PIPE G2 L900 HIGH OUTPUT NW
Technology	LED
Housing	PC Polycarbonate
General application	Residential & Consumer,
Operating temperature range (°C)	-20°C - 40°C

LED PIPE High OUTPUT

LED PIPE G2 L900 HIGH OUTPUT NW
0051048

Certifications	EUNEW009
ETIM Class	EC000109
E-number SE	7505155

Optical data

Fixture luminous flux (lm)	1500
Luminaire efficacy (lm/W)	115
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Beam angle (Rated) (°)	150
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	13
Mains voltage (V)	220-240V~
Lamp power factor	0.9
Electrical protection	Class II
Dimmable	N
Drive current (mA)	125
Inrush Current (A)	2
Inrush Duration (µs)	50
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	15
Max. Luminaires per 13A C Breaker	15
Max. Luminaires per 16A C Breaker	15
Max. Luminaires per 20A C Breaker	15
Max. Luminaires per 10A B Breaker	10
Max. Luminaires per 13A B Breaker	13
Max. Luminaires per 16A B Breaker	15
Max. Luminaires per 20A B Breaker	15

Lifetime data

Lumen maintenance - L70 B50	30000
-----------------------------	-------

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	900
Nominal Product Width (mm)	24
Nominal Product Height (mm)	35
Weight (kg)	0.228

Packaging


Single packaging type	Carton
Product EAN number	5410288510484

LED PIPE High OUTPUT


LED PIPE G2 L900 HIGH OUTPUT NW
0051048

Packaging single length / height (cm)	4.1
Packaging single width (cm)	3.2
Packaging single depth (cm)	102.0
DUN14 (outer)	15410288510481
Units per outer package	20
Packaging outer length / height (cm)	104.0
Packaging outer width (cm)	18.5
Packaging outer depth (cm)	19.0

PHOTOMETRY





TECHNICAL DRAWINGS




LED PIPE High OUTPUT LED PIPE G2 L900 HIGH OUTPUT NW 0051048


SYLVANIA 0051048


 This luminaire contains built-in LED lamps

 } LED


The lamps cannot be changed in the luminaire.

874/2012 

 This luminaire contains built-in LED lamps

 } LED

The lamps cannot be changed in the luminaire.

SYLVANIA 0051048 

874/2012