

# PRO-ELEC



## Fence Lights

### Model: PEL01340 and PEL01341

Please read these instructions carefully before use and retain for future reference.

#### IMPORTANT SAFETY INFORMATION

- Avoid locations of high temperature or humidity.
- The lamp is rated at IP55 for external use.

#### WHAT'S INCLUDED


- Lamp assembly.
- User manual.
- Pack of screws and wall plugs.

#### POSITIONING

- The lamp is suitable for mounting on plasterboard, wood or masonry surfaces.
- It should be mounted at approximately 1.5metres above the ground for best performance of the motion sensor.
- Before drilling any fixing holes, check that there are no hidden obstructions behind the mounting surface such as pipes or cables.

#### INSTALLATION

- Remove the lens by prising it away using a flat blade screwdriver.
- Offer the lamp to the surface and mark the location of the fixing holes.
- Drill the wall if required, fit the wall plugs then attach the lamp using the screws provided.
- Switch the lamp on using the slide switch then refit the lens.



## OPERATION

- **Allow at least 8hrs for the battery to fully charge initially.**
- The lamp will illuminate for approximately 30 seconds during low light levels if it detects motion presence or sound of voices in close proximity.

## CLEANING & MAINTENANCE

- Clean the unit only with a soft dry cloth. Do not use any chemicals, abrasives or solvents that could damage the casing or lens.
- During periods where the lamp may not be used, it is advisable to charge the battery occasionally to maintain its performance and before re-using the lamp.

## SPECIFICATION

- Battery: Ni-MH AA 1.2V 1000mAh rechargeable.
- Light source : 6 LED 20lm.
- Solar plate : poly-silicon 2V/130mA.
- Charge time : >8H.



### INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.



Made in China. PR2 9PP

Man Rev 1.1