## Cable Assembly U.FL - SMA, IP67, 200mm

# multicomp PRO


### RoHS Compliant



#### **Specifications:**

Connector Type A	: U.FL
Connector Type B	: SMA
Impedance	: 50Ω
Frequency Range	: DC to 3GHz
Maximum Working Voltage	: 60V rms
Min. Dielectric Withstanding Voltage	: 200V rms
Min. Insulation Resistance	: 500MΩ
Cable Assembly Type	: RF Coaxial
Cable Length	: 200mm
External Diameter	: 1.37mm
Cable Colour	: Black

#### Diagram



**Dimensions : Millimetres** 

Item	Description	
1	SMA B/H Jack Crimp Type for \$1.37mm Cable (Nut × 1, Washer × 1)	
2	Heat Shrink Tube F32 ¢2.5mm L = 10mm Colour: Black	
3		
4	U.FL-LP-088 Shell for	
5	U.FL-LP-088 Terminal for	

#### Part Number Table

Description	Part Number
Cable, U.FL - SMA, IP67, Length 200mm	R-132G7210200CB

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farrell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

