

- **Ultra-wide 12:1 input voltage range 9–75, 14–160 VDC**
- **Compact 2.3"x1.45"x0.5" standard package (quarter brick)**
- **Bus pin to easily extend hold-up time**
- **EN 50155 and EN 61373 approval for railway applications**
- **Qualification for fire behavior according to EN 45545-2**
- **Operating temperature range -40°C to +75°C**
- **I/O-isolation 3'000 VAC**
- **High efficiency up to 91%**
- **Adjustable output voltage, Remote On/Off and adjustable under voltage lockout**
- **3 year product warranty**



The TEP 60UIR is a series of high performance 60 Watt railway DC/DC converters with ultra wide 12:1 input voltage range featuring a compact ¼ brick (2.3"x1.45"x0.5") metal package. The ultra wide input allows the converter to act as an all-in-one solution if different voltage ranges have to be covered in the same application, resolving the issue of having multiple different converters installed. An internal circuit implemented in these modules helps to extend the hold-up time with ease as it eliminates the need of expensive high voltage capacitors to cover the full input range. With only a 25V capacitor (independent of the input voltage) the whole input range can be covered effectively reducing cost, size and inrush current. All models are approved for railway applications according to EN 50155, EN 61373, EN 45545-2 and offer standard features such as high efficiency up to 91%, an operating temperature range of -40° to +75°C and an I/O-isolation voltage of 3'000 VAC. An adjustable under voltage lockout function, remote on/off and adjustable outputs round out the features and ensure that these converter modules fit in any application setup.

| Models         |                               |                     |                     |                 |
|----------------|-------------------------------|---------------------|---------------------|-----------------|
| Order Code     | Input Voltage Range           | Output Voltage nom. | Output Current max. | Efficiency typ. |
| TEP 60-3611UIR | 9 - 75 VDC<br>(36 VDC nom.)   | 5 VDC               | 12'000 mA           | 89 %            |
| TEP 60-3612UIR |                               | 12 VDC              | 5'000 mA            | 89 %            |
| TEP 60-3613UIR |                               | 15 VDC              | 4'000 mA            | 90 %            |
| TEP 60-3615UIR |                               | 24 VDC              | 2'500 mA            | 90 %            |
| TEP 60-3618UIR |                               | 48 VDC              | 1'250 mA            | 91 %            |
| TEP 60-7211UIR | 14 - 160 VDC<br>(72 VDC nom.) | 5 VDC               | 12'000 mA           | 89 %            |
| TEP 60-7212UIR |                               | 12 VDC              | 5'000 mA            | 89 %            |
| TEP 60-7213UIR |                               | 15 VDC              | 4'000 mA            | 89 %            |
| TEP 60-7215UIR |                               | 24 VDC              | 2'500 mA            | 90 %            |
| TEP 60-7218UIR |                               | 48 VDC              | 1'250 mA            | 90 %            |

| Options  |  |
|--|--|
| TEP-HS2  | - Optional Heat Sink: <a href="http://www.tracopower.com/products/tep-hs2.pdf">www.tracopower.com/products/tep-hs2.pdf</a>   |
| TEP-HS4  | - Optional Heat Sink: <a href="http://www.tracopower.com/products/tep-hs4.pdf">www.tracopower.com/products/tep-hs4.pdf</a>   |
| on demand<br>(backorder with MOQ<br>non stocking item) | - Heat Sink (large profile): <a href="http://www.tracopower.com/products/tep-hs3.pdf">www.tracopower.com/products/tep-hs3.pdf</a><br>- Heat Sink (large profile): <a href="http://www.tracopower.com/products/tep-hs5.pdf">www.tracopower.com/products/tep-hs5.pdf</a> |

## Input Specifications

|                        |              |   |
|------------------------|--------------|---|
| Input Current          | - At no load | 36 Vin models: <b>20 mA typ.</b><br>72 Vin models: <b>17 mA typ.</b>  |
| Surge Voltage          |              | 36 Vin models: <b>100 VDC max.</b> (1 s max.)<br>72 Vin models: <b>185 VDC max.</b> (1 s max.)  |
| Start-up Voltage       |              | 36 Vin models: <b>9 VDC</b><br>72 Vin models: <b>14 VDC</b><br><br>(The Start-up voltage as well as the Shutdown voltage can be adjusted by a resistor between UVLO and -Vin pins.<br>see application note:<br><a href="http://www.tracopower.com/overview/tep60uir">www.tracopower.com/overview/tep60uir</a> ) |
| Under Voltage Lockout  |              | 36 Vin models: <b>7.3 VDC min. / 7.7 VDC typ. / 8.1 VDC max.</b><br>72 Vin models: <b>10 VDC min. / 11 VDC typ. / 12 VDC max.</b>   |
| Recommended Input Fuse |              | 36 Vin models: <b>12'000 mA</b> (fast acting)<br>72 Vin models: <b>8'000 mA</b> (fast acting)<br><br>(The need of an external fuse has to be assessed in the final application.)  |
| Input Filter           |              | <b>Internal Pi-Type</b>   |

## Output Specifications

|  |  |   |
|--|--|---|
| Output Voltage Adjustment              |  | -20% to +10% (By external trim resistor)<br><br>See application note: <a href="http://www.tracopower.com/overview/tep60uir">www.tracopower.com/overview/tep60uir</a><br>Output power must not exceed rated power!   |
| Voltage Set Accuracy                   |  | <b>±1% max.</b>   |
| Regulation                             | - Input Variation (Vmin - Vmax)<br>- Load Variation (0 - 100%) | <b>0.1% max.</b><br><b>0.1% max.</b>  |
| Ripple and Noise<br>(20 MHz Bandwidth) |  | 5 Vout models: <b>75 mVp-p typ.</b> (w/ 1 µF X7R // 22 µF poscap)<br>12 Vout models: <b>100 mVp-p typ.</b> (w/ 22 µF X7R)<br>15 Vout models: <b>100 mVp-p typ.</b> (w/ 22 µF X7R)<br>24 Vout models: <b>200 mVp-p typ.</b> (w/ 4.7 µF X7R)<br>48 Vout models: <b>300 mVp-p typ.</b> (w/ 2.2 µF X7R) |
| Capacitive Load                        |  | 5 Vout models: <b>24'000 µF max.</b><br>12 Vout models: <b>4'200 µF max.</b><br>15 Vout models: <b>2'700 µF max.</b><br>24 Vout models: <b>1'100 µF max.</b><br>48 Vout models: <b>260 µF max.</b>  |
| Minimum Load                           |  | <b>Not required</b>   |
| Temperature Coefficient                |  | <b>±0.02 %/K max.</b>   |
| Hold-up Time                           |  | <b>10 ms min.</b> (acc. to EN 50155 Class S2<br>see application note for BUS connection:<br><a href="http://www.tracopower.com/overview/tep60uir">www.tracopower.com/overview/tep60uir</a> )  |
| Start-up Time                          |  | <b>75 ms typ. / 100 ms max.</b>   |
| Short Circuit Protection               |  | <b>Continuous, Automatic recovery</b>   |
| Output Current Limitation              |  | <b>120 - 140% of Iout max.</b>  |
| Overvoltage Protection                 |  | <b>120 - 135% of Vout nom.</b>  |
| Transient Response                     | - Response Time  | <b>250 µs typ.</b> (25% Load Step)  |

## Safety Specifications

|                  |                             |  |
|------------------|-----------------------------|--|
| Safety Standards | - IT / Multimedia Equipment | EN 62368-1<br>IEC 62368-1<br>UL 62368-1  |
|                  | - Railway Applications      | EN 50155   |
|                  | - Certification Documents   | <a href="http://www.tracopower.com/overview/tep60uir">www.tracopower.com/overview/tep60uir</a> |

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

## EMC Specifications

|                             |                           |  |
|-----------------------------|---------------------------|--|
| <b>EMI Emissions</b>        |                           | EN 50121-3-2 (EMC for Rolling Stock)   |
| - Conducted Emissions       |                           | EN 55032 class A (with external filter)  |
|                             |                           | EN 55032 class B (with external filter)  |
| - Radiated Emissions        |                           | EN 55032 class A (with external filter)  |
|                             |                           | EN 55032 class B (with external filter)  |
|                             | External filter proposal: | <a href="http://www.tracopower.com/overview/tep60uir">www.tracopower.com/overview/tep60uir</a> |
| <b>EMS Immunity</b>         |                           | EN 50155 (Railway Applications)  |
|                             |                           | EN 55024 (IT Equipment)  |
| - Electrostatic Discharge   | Air:                      | EN 61000-4-2, $\pm 8$ kV, perf. criteria A   |
|                             | Contact:                  | EN 61000-4-2, $\pm 6$ kV, perf. criteria A   |
| - RF Electromagnetic Field  |                           | EN 61000-4-3, 20 V/m, perf. criteria A   |
| - EFT (Burst) / Surge       |                           | EN 61000-4-4, $\pm 2$ kV, perf. criteria A   |
|                             |                           | EN 61000-4-5, $\pm 2$ kV, perf. criteria A   |
|                             | Ext. input component:     | 36 V models: 2 x KY 220 $\mu$ F  |
|                             |                           | 72 V models: 2 x KXJ 150 $\mu$ F   |
| - Conducted RF Disturbances |                           | EN 61000-4-6, 10 Vrms, perf. criteria A  |
| - PF Magnetic Field         | Continuous:               | EN 61000-4-8, 100 A/m, perf. criteria A  |
|                             | 1 s:                      | EN 61000-4-8, 1000 A/m, perf. criteria A   |

## General Specifications

|   |                                 |  |
|---|---------------------------------|--|
| <b>Relative Humidity</b>                      |                                 | 95% max. (non condensing)  |
| <b>Temperature Ranges</b>                     | - Operating Temperature         | -40°C to +75°C   |
|   | - Case Temperature              | +105°C max.  |
|   | - Storage Temperature           | -55°C to +125°C  |
| <b>Power Derating</b>                         | - High Temperature              | See application note: <a href="http://www.tracopower.com/overview/tep60uir">www.tracopower.com/overview/tep60uir</a> |
| <b>Over Temperature Protection Switch Off</b> | - Protection Mode               | 110°C typ. (Automatic recovery at 95°C typ.)   |
| <b>Cooling System</b>                         |                                 | Natural convection (20 LFM)  |
| <b>Sense Function</b>                         |                                 | 10% max. of $V_{out}$ nom.<br>(If sense function is not used, sense pins should be connected to output pins.)        |
| <b>Remote Control</b>                         | - Voltage Controlled Remote     | On: 0 to 1.2 VDC or short circuit<br>Off: 3 to 12 VDC or open circuit<br>Refers to 'Remote' and '-Vin' Pin           |
|   | - Off Idle Input Current        | 3 mA typ.  |
|   | - Remote Pin Input Current      | -0.5 to 1.0 mA   |
| <b>Switching Frequency</b>                    |                                 | 160 - 200 kHz<br>180 kHz typ.  |
| <b>Insulation System</b>                      |                                 | Reinforced Insulation (72 Vin models)<br>Basic Insulation (36 Vin models)  |
| <b>Isolation Test Voltage</b>                 | - Input to Output, 60 s         | 3'000 VAC (72 Vin models)<br>2'250 VDC (36 Vin models)   |
|   | - Input to Case, 60 s           | 1'500 VAC (72 Vin models)<br>1'600 VDC (36 Vin models)   |
|   | - Output to Case, 60 s          | 1'500 VAC (72 Vin models)<br>1'600 VDC (36 Vin models)   |
| <b>Isolation Resistance</b>                   | - Input to Output, 500 VDC      | 1'000 M $\Omega$ min.  |
| <b>Isolation Capacitance</b>                  | - Input to Output, 100 kHz, 1 V | 1'000 pF max.  |
| <b>Reliability</b>                            | - Calculated MTBF               | 738'000 h (MIL-HDBK-217F, ground benign)   |
| <b>Environment</b>                            | - Vibration                     | MIL-STD-810F<br>EN 61373   |
|   | - Thermal Shock                 | MIL-STD-810F<br>EN 61373   |
| <b>Housing Material</b>                       |                                 | Alu base-plate w. plastic case   |
| <b>Potting Material</b>                       |                                 | Silicone (UL 94 V-0 rated)   |

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.


|                          |  |
|--------------------------|--|
| Connection Type          | THD (Through-Hole Device)  |
| Weight                   | 64 g   |
| Thermal Impedance        | 8.27 K/W   |
| Environmental Compliance | - Reach<br>- RoHS<br>- Flammability (EN 45545-2)   |
|                          | <a href="http://www.tracopower.com/info/reach-declaration.pdf">www.tracopower.com/info/reach-declaration.pdf</a><br><a href="http://www.tracopower.com/info/rohs-declaration.pdf">www.tracopower.com/info/rohs-declaration.pdf</a><br><a href="http://www.tracopower.com/info/en45545-declaration.pdf">www.tracopower.com/info/en45545-declaration.pdf</a> |

### Supporting Documents

Overview Link (for additional Documents)

[www.tracopower.com/overview/tep60uir](http://www.tracopower.com/overview/tep60uir)

### Outline Dimensions



Pin (4, 8): 1.5 (0.06)  
Pin (other): 1.0 (0.04)

Dimensions in mm (inch)  
Tolerances: x.x ±0.5 (±0.02)  
x.xx ±0.25 (±0.01)  
Pin diameter ±0.1 (±0.004)  
Screw lock torque: Max. 0.34 N·m (3.5 kgf·cm)

### Pinout

| Pin | Signal        |
|-----|---------------|
| 1   | -Vin (GND)    |
| 2   | Remote On/Off |
| 3   | +Vin (Vcc)    |
| 4   | -Vout         |
| 5   | -Sense        |
| 6   | Trim          |
| 7   | +Sense        |
| 8   | +Vout         |
| 9   | Bus           |
| 10  | UVLO          |