

AFBR-S4N33C013

NUV-HD Single Silicon Photo Multiplier




Description

The Broadcom® AFBR-S4N33C013 is a single silicon photo multiplier (SiPM) used for ultra-sensitive precision measurement of single photons. The active area is $3.0 \times 3.0 \text{ mm}^2$. High packing density of the single chips is achieved using through-silicon-via (TSV) technology and a chip-sized package (CSP). Larger areas can be covered by tiling multiple AFBR-S4N33C013 CSPs almost without any edge losses. The protective layer is made by a glass highly transparent down to UV wavelengths, resulting in a broad response in the visible light spectrum with high sensitivity towards blue- and near-UV region of the light spectrum. The AFBR-S4N33C013 SiPM is best suited for the detection of low-level pulsed light sources, especially for detection of Cherenkov- or scintillation light from the most common organic (plastic) and inorganic scintillator materials (for example, LSO, LYSO, BGO, NaI, CsI, BaF, LaBr). This product is lead free and compliant with RoHS.

Block Diagram

Figure 1: AFBR- S4N33C013 Block Diagram



Features


- High PDE of more than 54% at 420 nm
- Chip-sized package (CSP)
- Excellent SPTR and CRT
- Excellent uniformity of breakdown voltage, 180 mV (3 sigma)
- Excellent uniformity of gain
- With TSV technology (4-side tilable), with high fill factors
- Size $3.14 \times 3.14 \text{ mm}^2$
- Cell pitch $30 \times 30 \text{ }\mu\text{m}^2$
- Highly transparent glass protection layer
- Operating temperature range from -40°C to $+85^\circ\text{C}$
- RoHS and REACH compliant

Applications

- X-ray and gamma ray detection
- Gamma ray spectroscopy
- Safety and security
- Nuclear medicine
- Positron emission tomography
- Life sciences
- Flow cytometry
- Fluorescence – luminescence measurements
- Time correlated single photon counting
- High energy physics
- Astrophysics

Pad Layout and Soldering Ball Geometry


Figure 2: Redistribution Layer, Pad Layout, and Soldering Ball Geometry



All dimensions are in millimeters. A stands for anode, C stands for cathode. All cathode balls (C_1 to C_2) are connected together. All anodes (A_1 to A_2) are connected together. R_1 and R_2 are connected together. Unlabeled balls and R_1 - R_2 are floating, preferred electrical connection to cathode voltage.

Reflow Soldering Diagram

Figure 3: Recommended Reflow Soldering Profile



Absolute Maximum Ratings

Stresses in excess of the absolute maximum ratings can cause damage to the devices. Limits apply to each parameter in isolation. Absolute maximum ratings are those values beyond which damage to the device may occur if these limits are exceeded for other than a short period of time.

| Parameter | Symbol | Min. | Max. | Units |
|--|-------------|------|------|-------|
| Storage Temperature | T_{STG} | -40 | +85 | °C |
| Operating Temperature | T_A | -40 | +85 | °C |
| Soldering Temperature ^{a, b} | T_{SOLD} | — | 245 | °C |
| Lead Soldering Time ^{a, b} | t_{SOLD} | — | 60 | s |
| Electrostatic Discharge Voltage Capability HBM | ESD_{HBM} | — | 2 | kV |
| Electrostatic Discharge Voltage Capability CDM | ESD_{CDM} | — | 500 | V |
| Operating Over Voltage | V_{OV} | — | 10 | V |

a. The AFBR-S4N33C013 is reflow-solderable according to solder diagram as shown in [Figure 3](#).

b. According to JEDEC J-STD-020D, the moisture sensitivity classification is MSL3.

Device Specification

Features measured at 25°C unless otherwise specified.

Geometric Features

| Parameter | Symbol | Value | Units |
|------------------------|--------------------|-------------|-----------------|
| Device area | DA | 3.14 × 3.14 | mm ² |
| Active area | AA | 3.0 × 3.0 | mm ² |
| Micro cell pitch | L _{cell} | 30 | μm |
| Number of micro cells | N _{cells} | 9815 | — |
| Micro cell fill factor | FF | 76 | % |

Optical and Electrical Features

Two recommended working points: "Typical" for general-purpose applications and "Performance" for best timing performance.

| Parameter | Symbol | Min. | Typ. | Max. | Units | Reference Plots |
|--|--------------------------|------|------|------|-------|--------------------------|
| Spectral range | λ | 300 | — | 900 | nm | |
| Peak sensitivity wavelength | λ_{PK} | — | 420 | — | nm | Figure 4 |
| Breakdown voltage | V _{bd} | — | 26.9 | — | V | Figure 6 |
| Temperature coefficient of breakdown voltage | $\Delta V_{BR}/\Delta T$ | — | 26 | — | mV/K | |

| Parameter | Symbol | Typ. ^a | Perf. ^a | Units | Reference Plots |
|--|-------------------------------|-------------------|--------------------|----------------------|-------------------------------------|
| Photo detection efficiency ^b | PDE | 43 | 54 | % | Figure 5 |
| Dark current | I _D | 0.3 | 2.3 | μA | Figure 6 |
| Dark count rate ^c | DCR | 1.0 | 2.3 | Mcps | Figure 7, Figure 10 |
| Dark count rate per unit area | DCR _{mm²} | 111 | 255 | kcps/mm ² | |
| Gain | G | 1.6 | 3.2 | × 10 ⁶ | Figure 8, Figure 11 |
| Optical crosstalk | P _{Xtalk} | 11 | 34 | % | Figure 9 |
| After pulsing probability | P _{AP} | <1 | 1 | % | Figure 9 |
| Recharge time constant ^d | τ_{fall} | 57 | 48 | ns | |
| Nominal terminal capacitance ^e | CT | 645 | 498 | pF | |
| Temperature coefficient of gain ^f | $\Delta G/\Delta T$ | 1.1 | 0.9 | × 10 ⁴ /K | |

a. Typical values are measured at 3V above breakdown, performance at 7V above breakdown.

b. Measured at peak sensitivity-wavelength. Measurement does not include correlated noise, such as afterpulsing or optical crosstalk.

c. Measured at 0.5 p.e. amplitude. Measurement does not include delayed correlated events.

d. Measured on 1 × 1 mm² devices with an input impedance of 20Ω.

e. Measured using input sine wave with f = 200 kHz and V_{in} = 500 mV.

f. Calculated from gain dependence on V and breakdown voltage temperature coefficient: $dG/dT = dG/dV \times dV_{BR}/dT$.

Reference Plots

Features measured at 25°C unless otherwise specified.

Figure 4: Spectral Sensitivity




Figure 5: PDE at Peak λ vs. OV




Figure 6: Typical Reverse IV Curve





Figure 7: Dark Count Rate vs. OV



Reference Plots (continued)

Features measured at 25°C unless otherwise specified.

Figure 8: Gain vs. OV




Figure 9: Correlated Noise vs. OV




Figure 10: Dark Count Rate vs. PDE at Peak λ





Figure 11: Gain vs. PDE at Peak λ



Broadcom, the pulse logo, Connecting everything, Avago Technologies, Avago, and the A logo are among the trademarks of Broadcom and/or its affiliates in the United States, certain other countries, and/or the EU.

Copyright © 2018–2020 Broadcom. All Rights Reserved.

The term “Broadcom” refers to Broadcom Inc. and/or its subsidiaries. For more information, please visit www.broadcom.com.

Broadcom reserves the right to make changes without further notice to any products or data herein to improve reliability, function, or design. Information furnished by Broadcom is believed to be accurate and reliable. However, Broadcom does not assume any liability arising out of the application or use of this information, nor the application or use of any product or circuit described herein, neither does it convey any license under its patent rights nor the rights of others.

