

DIN rail bus connectors - ME 17,5 TBUS 1,5/ 5-ST-3,81 GN - 2709561

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




DIN rail connector for DIN rail mounting. Universal for TBUS housing. Gold-plated contacts, 5-pos.

Your advantages

- For bridging the supply voltage when using a MINI POWER system power supply unit



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| GTIN |  4 017918 892654 |
| GTIN | 4017918892654 |
| Weight per Piece (excluding packing) | 5.100 g |
| Custom tariff number | 85366990 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|------------------|---------|
| Installed height | 20 mm |
| Width | 3.5 mm |
| Pitch | 3.81 mm |

Technical data

| | |
|----------------------------------|-------|
| Connection in acc. with standard | CUL |
| Nominal voltage U_N | 150 V |
| Nominal current I_N | 8 A |
| Indicator1 | CUL1 |
| Number of positions | 5 |

Standards and Regulations

| | |
|----------------------------------|-----|
| Connection in acc. with standard | CUL |
|----------------------------------|-----|

DIN rail bus connectors - ME 17,5 TBUS 1,5/ 5-ST-3,81 GN - 2709561

Technical data

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27240692 |
| eCl@ss 4.0 | 27260700 |
| eCl@ss 4.1 | 27260700 |
| eCl@ss 5.0 | 27260700 |
| eCl@ss 5.1 | 27260700 |
| eCl@ss 6.0 | 27260700 |
| eCl@ss 7.0 | 27440309 |
| eCl@ss 8.0 | 27440402 |
| eCl@ss 9.0 | 27240692 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001031 |
| ETIM 3.0 | EC001031 |
| ETIM 4.0 | EC002638 |
| ETIM 5.0 | EC002637 |
| ETIM 6.0 | EC002584 |
| ETIM 7.0 | EC002584 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 31261501 |
| UNSPSC 7.0901 | 31261501 |
| UNSPSC 11 | 31261501 |
| UNSPSC 12.01 | 31261501 |
| UNSPSC 13.2 | 39121409 |
| UNSPSC 18.0 | 39121552 |
| UNSPSC 19.0 | 39121552 |
| UNSPSC 20.0 | 39121552 |
| UNSPSC 21.0 | 39121552 |

Approvals

Approvals

DIN rail bus connectors - ME 17,5 TBUS 1,5/ 5-ST-3,81 GN - 2709561

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approval details

| | | |
|--------------------|--|--|
| UL Recognized | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E118976-20151204 |
| Nominal voltage UN | | 150 V |
| Nominal current IN | | 8 A |

| | | |
|--------------------|--|--|
| cUL Recognized | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E118976-20151204 |
| Nominal voltage UN | | 150 V |
| Nominal current IN | | 6 A |

| | | |
|-----|--|---------|
| EAC | | B.01742 |
|-----|--|---------|

| | |
|------------------|--|
| cULus Recognized | |
|------------------|--|