PD SCAN

Handheld scanner for PD surveying in MV and HV plants



- For fast verification of partial discharge activity in MV and HV plants
- Universal application range, thanks to wide variety of sensors
- Integrated camera and QR code scanner
- Easy to use via keypad and touchscreen
- Reporting via MeggerBook RE software

DESCRIPTION

Defects in medium and high voltage systems not only require costly repairs, but can lead to failures of network sections with corresponding consequences. Therefore, it is in the interest of all network operators to recognize signs of impending defects as early as possible and to be able to take appropriate countermeasures on time.

With the PD Scan, Megger offers a lightweight, robust and portable PD scanner that can quickly inspect various types of equipment for partial discharge signals.

The PD Scan is used for the early detection of partial discharges emanating from defects in medium voltage switchgears and other electric equipment. For this purpose, the device has two internal sensors (TEV, airborne acoustic) and can also be operated with various types of external sensors (TEV, HFCT, airborne acoustic, contact probes).

The operation of the device is simple; it can be controlled via the three soft keys as well as via the intuitive touch display. Thanks to the auto-recognition of the connected external sensor, malfunction operation, as well as bothersome browsing through individual screens, can be eliminated.

Thanks to the large variety of sensors, the PD Scan can be used for multiple application ranges. PD within the cable insulation can be detected using the HFCT sensor. Partial discharges in encapsulated switchgears can be measured by using the contact-probe sensor and corona and surface discharges in MV and HV systems can be identified with the parabolic acoustic sensor.

Besides the partial discharge sensors, also a temperature and humidity sensor will be supplied. This is very important as the temperature and humidity can have a significant impact on the partial discharge readings. One of the advantages of the PD Scan is that the the sensor is connected directly to the device, meaning data is stored within the test files, removing the need to manually add them later on during the reporting stage.



The variety of sensors have made this handheld scanner a unique measuring device. To support the end user, measurement data will be automatically evaluated and interpreted, and pictures of the identified defects can be made and directly integrated into the report by using the integrated camera. Furthermore, the QR code scanner can directly take over the switchgear/asset data; there is no need to inconveniently rename the folder for each different test object. Make life easier by reducing the number of loose cables in the workspace through using the optional (and comfortable) Bluetooth® headset, which can also be used with a helmet.

Establishing detailed and individual test reports can be performed quickly by using the supplied MeggerBook RE reporting software.

Online PD handheld scanner

Megger.

TECHNICAL DATA

PD SCAN

TEV Measurement (capacitive)

Measurement range -10 ... 80 dBmV
Bandwidth 2 ... 80 MHz
Resolution 1 dBmV
Accuracy ±1 dBmV

Acoustic sensor

Measurement range -10 ... 70 dBμVResolution 1 dBμVAccuracy $\pm 1 dBμV$

Transducer centre frequency 30, 40 and 80 kHz

HFCT sensor (inductive)

Measurement range -10 ... 80 dB Bandwidth 100 kHz ... 20 MHz

Resolution 1 dB

Accuracy $\pm 1 \text{ dB/} < \pm 10\%$ Impedance 50 ohm

HousingInjection mouldedDisplay3.5 inch touchscreen,

320 x x240 pixel

Interfaces Lemo (external sensors)

USB type C (charging, head-

phone, PC) Bluetooth®

Control via 3 soft keys and touchscreen

IP rating IP 54

Temperature

Operation $-10 \dots 55 \,^{\circ}\text{C}$ Storage $-20 \dots 70 \,^{\circ}\text{C}$ **Relative humidity** 93 % at 30 $^{\circ}\text{C}$ (non-condensing)

Power supply

Charger Input voltage 90 ... 264 V,

50/60 Hz

Output voltage 5 VDC

Internal battery Li-lon 3.6 V / 3.35 Ah

Operating time > 8 hours Charging time ± 2 hours

Dimensions (W x H x D)

PD Scan 220 x 80 x 30 mm

Case STD 422 x 366 x 107 mm

Case PRO 512 x 445 x 313 mm

Weight

 PD Scan
 420 g

 Koffer STD
 940 g

 Koffer PRO
 3400 g

FEATURES

- Three PD measurement methods in one device
- Plug and Play; PD Scan automatically recognizes which external sensor has been connected
- Easy to use via soft keys and touchscreen
- Universal operating range due to large variety of sensor
- Automatic evaluation and interpretation of the results
- Optional comfortable Bluetooth® headphones
- Integrated camera
- QR Code scanner for asset recognition
- Different views and PRPD display for defect type recognition
- Temperature and humidity measurement using supplied sensor with storage on PD Scan itself
- MeggerBook RE reporting software



Set 1: Switchgear basic

The basic set is ideally suited for users who only want to concentrate on MV plant

Set 2: Switchgear basic + cable

The basic set + cable is ideally suited for users who want to concentrate on MV plant and cable

Set 3: Switchgear pro + cable

In addition to the HFCT and standard sensors, the pro set additionally contains external acoustic sensors for a more detailed analysis of MV plant

Set 4: Switchgear pro + cable + outdoor

The complete set for those who want to use all the functionalities of the device

ORDERING INFORMATION

Product Order no.

PD Scan Set 1 Switchgear Basis

1011121

PD Scan main device, external TEV sensor, temperature and humidity sensor, function tester, charger + USB cable, Bluetooth® headphone, transport case STD, USB Stick with operating manual and reporting software

PD Scan Set 2 Switchgear Basic + Cable

1011122

PD Scan main device, HFCT sensor, external TEV sensor, temperature and humidity sensor, function tester, charger + USB cable, Bluetooth® headphone, transport case STD, USB Stick with operating manual and reporting software

PD Scan Set 3 Switchgear Pro + Cable

1011123

PD Scan main device, flexible acoustic sensor, acoustic-contact probe, HFCT sensor, external TEV sensor, temperature and humidity sensor, function tester, charger + USB cable, Bluetooth® headphone, transport case PRO, USB Stick with operating manual and reporting software

PD Scan Set 4 Switchgear Pro + Cable + Outdoor

1011124

PD Scan main device, Parabolic receiver, flexible acoustic sensor, acoustic-contact probe, HFCT sensor, external TEV sensor, temperature and humidity sensor, function tester, charger + USB cable, Bluetooth® headphone, transport case PRO, USB Stick with operating manual and reporting software

Options:

Upgrade kit Set 1 to Set 4

1011550

Parabolic receiver, flexible acoustic sensor, acoustic-contact probe, HFCT sensor, Bluetooth® headphone and transport case PRO

Upgrade kit Set 2 to Set 4

PD Scan demonstrator box


1011551

Parabolic receiver, flexible acoustic sensor, acoustic-contact probe, Bluetooth® headphone and transport case PRO

1011423

PD Scan demonstrator, transport case and batteries	
Optional accessories:	
HFCT SC40, HF Current Transformer	1009667
VK 132, connection cable HFCT for PD Scan	90026538
TEV C900-PD Scan, external TEV sensor	1010524
AA FR130, flexible receiver	1009757
ACP 30, Piezo acoustic sensor	1010420
AA PR400, parabolic receiver	1009681
THS 55; temperature humidity sensor PD Scan	1010217
FC 1; function tester PD Scan	1010219
Bluetooth® headphone	90019021
PDK-STD, transport case for PD Scan set 1 and 2	90026227
PDK-PRO, transport case for PD Scan set 3 and 4	90026229

^{*} We reserve the right to make technical changes.



SALES OFFICES

Megger GmbH

Obere Zeil 2 D-61440 Oberursel Germany T 0049 6171 92987-0 E info@megger.de

Seba Dynatronic Mess- und Ortungstechnik GmbH Dr.-Herbert-lann-Str. 6 96148 Baunach Germany T 0049 9544 68-0

E team.international@megger.de

PD-SCAN_DS_EN_V01

www.megger.com

The word 'Megger' is a registered trademark.

