




Creating Safe Work Solutions During COVID-19

SSK2-4SA-NB

▶ PRODUCTS FOR INDUSTRIAL AUTOMATION



Sanitation Solution Kit

4 STATION SCHEDULE APPLICATION

DXM1200 2.4 GHz 65 mW Controller

(4) DIRECT SELECT Nodes

(4) K70DXN2GYRQ

(4) Brackets LMB30LP

(5) PSW-24-1 Power Supplies

Batteries NOT Included

Part Number: 810118


SPECIFICATIONS

Feature: Hazardous Area	No
EtherNet/IP	Yes
Modbus RTU	Yes
Modbus/TCP	Yes
RS-232	No
RS-485	Yes
Wireless	Yes
Wireless Radio Frequency	2.4 GHz
Battery Type/Size	Lithium/C
Ships With Battery	No
Tree Topology	No


Power Supply	26 V dc 1.0 Amp
Voltage	10-30 V dc
Point-to-Point Topology	Yes
Point-to-Multipoint Topology	Yes
Relative Humidity	90% at 50° C
Min Op. Temperature (°C)	-20
Max Op. Temperature (°C)	50
Star Topology	Yes

COMPATIBLE PRODUCTS

BRACKET

	<p>LMB30LP</p> <p>Bracket: Right Angle, Low Profile; Fits M30 Base; 12 Gauge 300 Series Stainless Steel (No Hardware)</p>
------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------

70 MM ILLUMINATED INDICATOR LIGHTS: K70 SERIES

	<p>K70DXN2GYRQ</p> <p>K70 Wireless Indicator, 2.4 GHz; 3-Color Indicator; Voltage: 12-30 V dc; Environmental Rating: IP65; Colors: Green Yellow Red; Euro 5-pin Quick-Disconnect</p>
-------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

	<p>PSW-24-1</p> <p>DC Power Supply - Wall Mount; Input: 100 -240 V ac 50/60 Hz; Multi-blade outlet plug; Output: 24 V dc 1A; 2 m (6.5 ft) Euro 4-pin Connector; UL Listed Class 2</p>
-------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

DXM 100 SERIES

	<p>DXM1200-B1R3</p> <p>DXM1200 Controller ; IP67; DX80 ISM 2.4 GHZ Radio (PE5) ; LCD Display</p>
-------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------

DIRECT SELECT



DX80N2DSTS-NB

Wireless Operator Interface Node; 2.4 GHz 65mW; LCD Display 0-999; Multicolor Capacitive Touch; Batteries NOT Included



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America