

16 NEB/J 21 C

Power supply connectors




Power supply chassis socket, straight version, with break contact and solder eyes, for front side mounting


State: Active


1 of 3 01/2018



NEB/J 21 C







Environmental conditions

Temperature range -20 °C/+70 °C

Materials

Insulating body PF


Contact CuZn/CuSn, nickel-plated/silver-

plated

Housing ABS, HB according to UL94

Hexagonal nut PA







Mechanical data

Diameter opening6,3 mmDiameter center pin2,0 mmMating cycles≥ 5000Insertion force≤ 30 N¹Withdrawal force3-30 N¹

¹ measured with a gauge plug

Electrical data (at Tamb 20 °C)

 $\begin{array}{ll} \mbox{Contact resistance} & \leq 30 \ m\Omega \\ \mbox{Rated current} & 0,5 \ A \\ \mbox{Rated voltage} & 12 \ V \ DC \\ \mbox{Rated impulse voltage} & 500 \ V/60 \ s \\ \mbox{Insulation resistance} & \geq 100 \ M\Omega \\ \end{array}$

Associated products

Counterparts

 C 1633 02
 C 1633 03
 C NES/J 21

 C NES/J 21 W
 C NES/J 210
 C XNES/J 210

*a port in mounting plate

2 of 3



16 NEB/J 21 C

| Designation | Pole Number | PU (Pieces) | MDQ (Pieces) |
|-------------|-------------|-------------|--------------|
| NEB/J 21 C | 2 | 250 | 750 |

Packaging:

in bulk, in a cardboard box or a plastic bag

3 of 3 01/2018