2.54mm IDC Plug DIP Type Connector

multicomp PRO

RoHS

Compliant




Specifications

Current Rating
Voltage Rating
Max. Contact Resistance
Min. Insulation Resistance
Withstanding Voltage
Operating Temperature Range
Material and Finish
Insulator
Contact

- : 1 A AC / DC
- : 30V AC / DC
- : 20mΩ
- : 1,000MΩ
- : 500 V AC / minute
- : -40°C to +105°C
- : PBT, black
- : Copper alloy
- : Selective gold plated

Diagram



Part Number Table

Description	Positions	A (mm)	Part Number
2.54mm IDC Plug DIP Type Connector	10	18	1565522
	14	23.08	1565523
	16	25.62	1565524
	20	30.74	1565525
	26	38.32	1565526
	34	48.48	1565528
	40	56.1	1565529
	50	68.8	1565530

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

