

## **ASSEMtech Europe Ltd**

## PRODUCT DATA SHEET





Drawings not to scale All dimensions in mm

## **SPECIFICATION**

CONTACT FORM/STYLE		Closed
SWITCHING VOLTAGE	Max. Vac	120
SWITCHING CURRENT	Max. A	0.5
SWITCHING CAPACITY (RESISTIVE)	Max. VA	100
CONTACT RESISTANCE	Max. $m\Omega$	30
OPERATING ANGLE	Max. Deg°	45° ± 15°
OPERATING TEMPERATURE	Deg. °C	-37° + 100°
STORAGE TEMPERATURE	Deg. °C	-40° + 125°
CASE MATERIAL		Steel-tin plated
MOUNTING CLIPS		3ВН
FEATURES		Standard switch contact normally closed

NOTE: When cutting or bending switch leads it is important that the glass seal is not damaged. The cutting or bending point should be no closer than 3mm to the glass to metal seal and the lead should be supported between the cutting or bending point and the glass to metal seal.

## **TIP-OVER SWITCHES**

PART NUMBER CM1421-0

Rev. No.	Revision Note	Date	Signature
В	1998 Catalogue Page 11	1-1-98	RG

es B



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.

BS5750/ISO 9000 Reg. No. FM 21080