
TRIAD™01 Shielded Subminiature Circular Connectors



Product Facts

- Small and lightweight, shielded round connector system
- Panel mount PCB versions 180° and 90°
- Panel mount Solder Cup 180° versions
- Field serviceable male and female connectors--crimp and solder version--for on site connections
- Single and double ended overmoulded cable leads are available
- Customized assemblies are possible to make upon request
- Components for BUS applications available



Description

Where shielding is a requirement in medical or industrial applications there will be the use of $\mathsf{TRIAD}^\mathsf{TM}01$ a good decision. The small and lightweight system is available as panel mount headers with solid posts 180° and 90° for soldering on PC boards and also with solder cups for wire termination.

The PCB version has two board locks and the solder cup version has two solder tabs for grounding.

Through the three O-ring design on the panel mount connectors and in connection with the over-moulded cable assemblies, $TRIAD^{TM}01$ is a liquid and dust tight system according to IP65 protection class (DIN 40050). The reasonable shielding, the small diameters, the over-moulded connector with cable and the use of metallic parts makes $TRIAD^{TM}01$ also useable in harsh environments such as a factory where $TRIAD^{TM}01$ can be used in BUS applications such as CAN or MODULAR too.

Components such as T-Adapters and terminator plugs with a resistor are also available in different colors upon request (e.g. yellow and purple).

Specifications

Shell Protection Class (nested condition): IP65 acc. DIN 40050

Temperature Range: -40°C to +85°C

Mating Cycles: ≤500
Test Voltage: 625 V AC
Operating Voltage: 60 V AC
Contact Resistance: < 6 m ohm

Interlock: Screw Type

130-722 TO 131-090

TRIAD 01 is a subminiature circular connector system which can be used for applications where shielding is a requirement.

Beside the excellent shielding properties of TRIAD01 there is also a good resistance against UV beams because of the OPTAL0Y® plating for all metal shell parts.

TRIAD01 is a liquid- and dust-tight system according to IP65 protection-class (DIN 40050).




A 3xO-ring design of the TRIAD01 panel-mount-connectors is ideal for using the TRIAD01 system in smoke-analysis applications.

Special T-adaptors with either a TRIAD01 connector or a SUB-D connector as Interface-Plug are offering the usage of TRIAD01 for BUS wiring like for a CAN- or for a MOD-BUS.

Both systems consist of 3 items:

- 1 The T-Adaptor
- 2 The "Trunk"-Cable an overmoulded cable with 2 male connectors
- 3 Terminator-Plug




131-027 10090

730 941

TRIAD™ 01

Shielded Subminiature
Circular Connectors
Panel Mount Version



PCB layout for max. 1.6 mm thickness 180° (only for PCB pinversions)	3.1	1 2 2 2 2 2 2 2 2	5 5x72°= 360°	P. 7x51,4° = 360°	P. 7x51,4° = 360°
90°	2 12 12 12 12 12 12 12 12 12 12 12 12 12	12 12 12 12 12 12 12 12 12 12 12 12 12 1	3,2		
Arrangement of Contacts/Mating side pinversion.	Coding	Coding 1	Coding 1	Coding 1	Coding 1
Arrangement of Contacts/ Termination side pinversion. (For sockets, arrangement is mirror image of pin version)	15	15 4 00 1 3 00 2	15 5 0 1 2 4 3 2	15 (Exp. 2) (5 % 2)	15 (797) (79
No. of Contacts	3	4	5 Catalogue No.	7	8
Panel Mount 180° PCB version, pin	T04 0570 D02	T04 0570 D04		T04 0570 D07	
Panel Mount 180° PCB version, socket	T01-0570-P03 T01-0570-S03	T01-0570-P04 T01-0570-S04	T01-0570-P05	T01-0570-P07	T01-0570-P08
Panel Mount 90° PCB version, pin	T01-0560-P03	T01-0570-504	T01-0570-S05	T01-0570-S07	T01-0570-S08
Panel Mount 90° PCB version, socket	T01-0560-P03		T01-0560-P05	_	_
Panel Mount 180° Handsolder version, pin	T01-0580-P03	T01-0560-S04 T01-0580-P04	T01-0560-S05	— Tot 0500 nov	
Panel Mount 180° Handsolder version, pocket	T01-0580-F03	T01-0580-P04	T01-0580-P05 T01-0580-S05	T01-0580-P07	T01-0580-P08
Technical Data	3	4	5	701-0580-S07	T01-0580-S08
Termination				ering	0
Plating				· 4 µm	
Dielectric of insert				. 94-V2	
Shell protection class				DIN 40050	
Shell material				iZn	
Operating temperature range				o +85 °C	
Mating cycles				500	
Wire gage		max. 0.25 mm²			1.14 mm²
Rated current per contact		3 A			I A
Test voltage		500 V AC			V AC
Operating voltage		60 V AC			V AC
Contact resistance		< 3 m Ω			mΩ


Priority type available from stock


Minimum unit quantity: 25 pieces (500 pcs)





Shielded Subminiature
Circular Connectors
Panel Mount Version
























Shielded Subminiature
Circular Connectors
Cable Mount Plugs







Arrangement of Contacts					<u></u>	
mangament of contacts	(o) - o) -	(+ + + + + + + + + +	• •	• •	
No. of Contacts	3	4	5	7	8	
	***		Catalogue No.		-	
Assembly type, pin	T01-0550-P03	T01-0550-P04	T01-0550-P05	T01-0550-P07	T01-0550-P08	
Assembly type, socket	T01-0550-S03	T01-0550-S04	T01-0550-S05	T01-0550-S07	T01-0550-S08	
Technical Data	3	4	5	7	.8	
Termination			Solo	lering		
Plating				r 4 µm		
Dielectric of insert				L 94-V2		
Shell protection class				DIN 40050		
Shell material			Cı	ıZn		
Operating temperature range			-40 °C t	o +85 ° C	•	
Mating cycles			> !	500		
Wire gage		max. 0.25 mm ²		max. 0.	14 mm²	
Rated current per contact		3 A	1 A			
Test voltage		500 VAC			VAC	
Operating voltage		60 VAC		60 '		
Contact resistance		$<$ 3 m Ω			mΩ	


Priority type available from stock


Minimum unit quantity: 25 pieces

130-977-731-015 TRIADTM 01

TRIAD™ 01

Shielded Subminiature
Circular Connectors
Cable assemblies
with overmoulded Connectors







Arrangement of Contacts

0 0









No. of Contacts		3	4	5	7	8
	<u> </u>			Catalogue No.		
Cable length 1 m		T01-0599-B03-A	T01-0599-B04-A	T01-0599-B05-A	T01-0599-B07-A	T01-0599-B08-A
Cable length 3 m		T01-0599-B03-B	T01-0599-B04-B	T01-0599-B05-B	T01-0599-B07-B	T01-0599-B08-B
Cable length 5 m		T01-0599-B03-C	T01-0599-B04-C	T01-0599-B05-C	T01-0599-B07-C	T01-0599-B08-C
Technical Dat		3	4	5	7	8
Termination		•		So	Idering	

Plating		Tribor 4 µm
Dielectric of insert	- P	BT UL 94-V2
Shell protection class	IIP65	5 acc. DIN 40050
Shell material		CuZn
Operating temperature range	_4() °C to +85 ° C
Mating cycles		> 500
Wire gage	max. 0.25 mm²	max. 0.14 mm²
Rated current per contact	3 A	1 A
Test voltage	500 VAC	500 VAC
Operating voltage	60 VAC	60 VAC
Contact resistance	- < 3 mΩ	< 5 mΩ


Priority type available from stock


Minimum unit quantity: 10 pieces


972-058

TRIAD™ 01

Shielded Subminiature
Circular Connectors
Accessories and Specials
CAN-BUS Components:
Non-interrupted Power
Supply for Network Devices








Pin Plug Terminator Resistor Unit 120 Ω

Cable assemblies, with overmoulded connectors: shielded

Arrangement of Contacts

No. of Contacts




		Catalogue No.					
T-Adaptor	T01-05T-SSP03-T	T01-05T-SSP04-T	T01-05T-SSP05-T	T01-05T-SSP07-T	T01-05T-SSP08-T		
Terminator Resistor Unit	T01-05R-P03-120	-		-			
Technical Data	3	4	5	7	8		
Termination	•		Sol	dering	-		
Plating				or 4 um			
Dielectric of insert			PBT U	L 94-V2			
Shell protection class			IP65 acc.	DIN 40050			
Shell material			С	uZn			
perating temperature range	•		-40 °C	to +85 ° C			
Mating cycles			>	500			
Wire gage		max. 0.25 mm²		max. 0	1.14 mm²		
Rated current per contact		3 A			I A		
Test voltage		500 VAC			VAC		
Operating voltage		60 VAC			VAC		
Contact resistance		$< 3 m\Omega$			mΩ		


Priority type available from stock


Minimum unit quantity: 25 pieces




Shielded Subminiature
Circular Connectors
Accessories and Specials
MOD-BUS Components








Cable assemblies, with overmoulded connectors: shielded




Shielded Subminiature Circular Connectors Accessories and Specials **BUS-Cable Assemblies** with Overmoulded Connectors



60 VAC

 $<3\,\text{m}\Omega$





Priority type available from stock

Minimum unit quantity: 25 pieces

Contact resistance

Shielded Subminiature
Circular Connectors
Accessories and Specials
Dust Caps







No. of Contacts	3	4	5	7	8			
	Catalogue No.							
For Pin Plugs	T01-0500-P							
For Socket Connectors	T01-0500-S							
Technical Data	3	4	5	7	8			
Shell protection class	1P 65 acc. DIN 40050							
Shell material	CuZn							
Operating temperature range	-40 °C to +85 °C							

Priority type available from stock

Minimum unit quantity: 25 pieces