

AT175 Polycoated Cloth Tape

General description

A polycloth laminate tape with a white pressure sensitive, aggressive adhesive.

- Gloss finish.
- Easy tear.
- Easy unwind.
- Conformable to awkward shapes.
- Water resistant finish.
- Good abrasion resistance.
- Non-corrosive adhesive.
- High tack.
- Clean peel.
- Flexible.
- Strong.

Technical Details

Typical values

Thickness 0.23mm

Breaking Load 32 N/cm

Elongation 14%

Adhesion

Steel 5.5 N/cm

Self 3.5 N/cm

Moisture Vapour Permeability 20g/m²/24 hrs

Water Extract

pH 6.0 to 8.0


Chloride Max 0.01% as NaCl

Sulphate Max 0.01% as Na₂SO₄

Service Temp -50°C to +80°C

Application Temp +10°C to +45°C

Storage Temp +10°C to +25°C



NOTE

Except where indicated otherwise, the above figures are average values and should not be regarded as MAXIMUM or MINIMUM values for specification purposes. The Company reserves the right to improve products and any change in specification will result in a re-issue of the relevant 'Technical Data Sheet'. Customers should satisfy themselves that the tape is suitable for their requirements whether after such modifications or otherwise. Please check that you have the latest issue of the 'Technical Data Sheet'. All slitting and length tolerances are to British Standards. Before use the customer is advised to consult the Health & Safety Data Sheet produced by the company for this product, which is available on request.

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.

 **ADVANCE**
adhesive tapes



BS EN ISO 9002
Q05206



INVESTOR IN PEOPLE

AFERA

Association des Fabricants Européens de
Rubans Auto-Adhésifs.

Advance Tapes International Limited, PO Box 122,
Abbey Meadows, Leicester, LE4 5RA.
Tel: 0116 251 0191. Fax: 0116 265 2046. www.advancetapes.com



ISSUE NO: Tech-05 **ISSUE DATE:** August 1990

Product: **GENERAL PURPOSE POLYCOATED
CLOTH TAPE**

AT175

Applications: Splicing, jointing, weather-proofing, export carton sealing, drum sealing. Ideally suited for joining polythene and many uses in the insulation (HEVAC) industry. Not to be used for colour coding livestock, use Agritape AT560 identity and repair tape for this application.

This tape is not recommended for gas fire back plate sealing. Use AT163 closure plate tape to British Gas specification PRS10.

Description: A polythene coated fabric with a white pressure sensitive, aggressive high tack adhesive. This tape has the benefits of easy tear and unwind.

Colours: Please see shade card. (9 colours)

Technical Details:

Tape Thickness:	0.23mm
Breaking Load:	40 N/cm
Elongation at Break:	20%
Adhesion to Steel:	6.0 N/cm
Adhesion to Self:	2.6 N/cm
Moisture Vapour Permeability:	20g/m ² /24 hrs @ 38°C and 90% R.H.
Water Extract:	
pH:	6.0 to 8.0
Chloride:	0.01% as NaCl
Sulphate:	Less than 0.01% as Na ₂ SO ₄
Service Temperature:	-50°C to 80°C
Application Temperature:	10°C to 45°C
Recommended Storage Temperature:	12°C to 25°C
Shelf Life:	1 year*
*See Health & Safety Data Sheet 2.	

Note:

Except where indicated otherwise, the above figures are average values and should not be regarded as MAXIMUM or MINIMUM values for specification purposes. The Company reserve the right to improve products and any change in specification will result in a re-issue of the relevant "Product Information Sheet". Customers should satisfy themselves that the tape is suitable for their requirements whether after such modification or otherwise. Please check that you have the latest issue of the "Product Information Sheet". All slitting and length tolerances are to British Standards, but other tolerances are available by request.

Health & Safety:

Before use the customer is advised to consult the Health & Safety Data Sheet produced by the Company for this product and which is available on request.