



- DC fans with electronically commutated external rotor motor. Fully integrated commutation electronics. With electronic protection against reverse polarity and blocking.
- Metal fan housing and impeller.
- Air exhaust over struts. Rotational direction CCW looking at rotor.
- Electrical connection via leads AWG 22, TR 64. Stripped and tinned ends. Housing with ground lug for screw M4.
- Mass 600 g.

SERIES 5200

127x127x38mm

Air flow		Nominal Voltage		Noise		Sintec-Sleeve Bearings	Power Input	Nominal Speed	Temperature Range	Service Life L ₁₀ at 40 °C		Curve	Type
m ³ /h	CFM	V DC	V DC	dB(A)	beis	○/●	Watt	min ⁻¹	°C	Hours	Hours		
200	117.7	12	8...16	44	5.5	●	4.5	2800	-15...+72	70000 / 30000		1	5212
200	117.7	24	18...30	44	5.5	●	4.7	2800	-15...+72	70000 / 30000		1	5214
200	117.7	48	36...56	44	5.5	●	4.6	2800	-15...+72	70000 / 30000		1	5218

⊕ 48V Type with grounding screw M4x6 7500C.

