

20KEBS6BFPD

✓ ACTIVE


TE Internal #: 4-1609965-5

3-Phase Filters, Current Rating 20 A, Threaded Bolt Input, Threaded Bolt Output, DELTA (3 wire + ground), 520 VAC

[View on TE.com >](#)



EMI Filters > Power Line Filters > 3-Phase Filters



Current Rating: 20 A

Input Type: Threaded Bolt

Output Type: Threaded Bolt

Wiring Configuration: DELTA (3 wire + ground)

Voltage (Max): 520 VAC

Features

Product Type Features

Filter Type	3-Phase Power Line
Filtered	Yes
Input Type	Threaded Bolt
Output Type	Threaded Bolt

Configuration Features

Wiring Configuration	DELTA (3 wire + ground)
----------------------	-------------------------

Electrical Characteristics

Leakage Current (Max) (230VAC, 50Hz)	3
Current Rating	20 A
Voltage (Max)	520 VAC

Mechanical Attachment

Mount Style	Flanged
-------------	---------

Usage Conditions

Operating Temperature Range	-25 – 85 °C
-----------------------------	-------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Model / Part # 4-1609965-6
KEB 25A 1S NUT DELTA 520VAC 50HZ



TE Model / Part # 4-1609965-7
KEB 30A 1S NUT DELTA 520VAC 50HZ

Documents

Product Drawings
KEB 20A 1S NUT DELTA 520VAC 50HZ
English

CAD Files
3D PDF



3D

Customer View Model

[ENG_CVM_CVM_4-1609965-5_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1609965-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1609965-5_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[KEB SERIES](#)

English