

# Digital Tire Pressure Guage

pro-SIGNAL



Front View

Side Views

## Description

This unit is an ideal tool for tire pressure measurement. It has the advantages of light weight and compact structure. It is very easy to use. It can use to measure a vehicle's tire pressure for safe driving.

## Specifications

Range	: 0 PSI to 100 PSI
Accuracy	: $\pm 1.5$ PSI
Resolution	: 0.5 PSI
Units	: PSI, BAR, KPA, Kg/cm <sup>2</sup>
Auto Power Off	: About 60 seconds later
Power Supply	: One 3V CR2032 battery*
Product Size	: 148mm × 39mm × 31mm
Product weight	: About 40g

### \*Note

Battery to be ordered separately.

## Part Number Table

Description	Part Number
Digital Tire Pressure Gauge	TG101

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands  
Farnell.com/exclusive-brands  
Element14.com/exclusive-brands

pro-SIGNAL