

# High-pressure measuring instrument operated with smartphone

## testo 549i

---

Compact professional measuring instrument from the Testo Smart Probes series for use with smartphones/tablets

---

Measurement of high and low pressure

---

Low refrigerant loss thanks to hoseless application

---

Quick and easy installation at the pressure connection thanks to 45° angle

---

Measurement data analyzed and sent via testo Smart Probes App

---

Problem-free use at measuring points that are a long distance apart – Bluetooth® range up to 100 m

---



 Bluetooth®  
+ App

testo Smart Probes App  
for free download



In conjunction with a smartphone or tablet, the handy testo 549i high-pressure measuring instrument is suitable for servicing and troubleshooting on air conditioning and refrigeration systems, as well as for their installation. The measuring instrument can be quickly and easily attached directly to the pressure connection. The testo 549i makes it considerably easier to work on pressure connections that are a long distance apart, thanks to wireless connection to a smartphone or tablet. Also practical: since no hoses are needed for the measurements, no refrigerant is lost, or only a very small quantity.

And simultaneous use of the testo 115i clamp thermometer also enables calculation of individual refrigeration system parameters, such as superheating. Users can read off their measuring values conveniently via the testo Smart Probes App installed on the terminal device. In addition, the testo Smart Probes App enables automatic calculation of evaporation and condensation temperatures. All measurement data are presented either as a diagram or a table. Finally, the measurement data reports can be sent directly as pdf or Excel files.

## Technical data/accessories

### testo 549i

testo 549i, high-pressure measuring instrument operated with smartphone, including batteries and calibration protocol

Order no. 0560 2549 02



#### testo Smart Probes App

The App turns your smartphone/tablet into the display for the testo 549i. Both the operation of the measuring instrument and the display of the readings are achieved by Bluetooth® via the testo Smart Probes App on your smartphone or tablet – irrespective of the measuring location. In addition, you can use the App to create measurement reports, add photos and comments to these and send them by e-mail. For iOS and Android.

Sensor type	Pressure
Measuring range	-1 to 60 bar
Accuracy ±1 digit	0.5% of full scale value
Resolution	0.01 bar
Connection	7/16" – UNF
Overload rel.	65 bar

#### General technical data

Compatibility	requires iOS 8.3 or newer / Android 4.3 or newer  requires mobile terminal device with Bluetooth® 4.0
Storage temperature	-20 to +60 °C
Operating temperature	-20 to +50 °C
Battery type	3 micro batteries AAA
Battery life	130 hrs
Measurable media	CFC, HFC, HCFC, N, H <sub>2</sub> O, CO <sub>2</sub>
Dimensions	150 x 32 x 31 mm
Bluetooth® range	up to 100 m

#### Accessories

#### Order no.

testo Smart Case (refrigeration) for the storage and transport of 2 x testo 115i and 2 x testo 549i, dimensions 250 x 180 x 70 mm	0516 0240	
ISO calibration for testo 549i (5 points over measuring range)	300520 0018	