

TECHNICAL DATA SHEET

Part#: 9232E

Cutters - Small Oval Head - ★★★★★ - Carbon Steel

The 9232E five star Lazer Line[®] small oval optimum flush cutter has a cutting capacity of .00" - .00" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide smooth action.

• Precision Level	★★★★★
• Material	Carbon
• Surface Resistivity	10 ¹⁰ ohms/sq
• Shape	Round Head
• Type of Cut	Lazer Flush
• Group	Cutting Tools
• Cutting Capacity	36 - 20 AWG / .005 - .032" / .13 - .88 mm
• Blade Angle	14.25°
• Blade Length	.24" (6mm)
• Body Width	0.32" (8mm)
• Body Height	0.20" (5mm)
• OAL	4.25" (106.25mm)
• Weight (OZ)	3
• UPC	662847013416
• Schedule B	8203.20.60.60
• ECCN	EAR99
• UNSPSC Code	27111511
• Country of Origin	USA

