# RODUCT DATA

Date: February 2004 Information Sheet No.: ZB0006

# **BOSTIK ARALDITE® RAPID SYRINGE**

# TWO PART, MULTIPURPOSE, EPOXY RESIN ADHESIVE

ARALDITE® RAPID is a two-part adhesive supplied a syringe. It is a powerful adhesive with a fast setting time for rapid bonding. It is solvent free, room temperature curing, high strength adhesive.

#### RECOMMENDED USES

ARALDITE® RAPID will bond a variety of materials around the home including metal, wood, ceramics, masonry, glass, dry concrete, chipboard, leather, cardboard and most hard plastics, fabrics and rubbers.

IMPORTANT: ARALDITE® RAPID is not suitable for bonding rearview mirrors to car windscreens. Do not use for items which may contain food or drink, as the joint however secure and clean it may appear, may entrap bacteria from the environment. Not intended for repairs on safety critical items e.g. rotating parts of hover mowers. Please note that some items are moulded from polymers such as polythene or polypropylene, for example, and are simply not designed for repair. Repair may not be viable or would need specialist chemical treatment to achieve a bond.

#### BONDING INSTRUCTIONS

- Make sure surfaces are dry, clean and free from dust, dirt and grease. For even better bonding slightly roughen surfaces with
- 2. Remove the cap from centre of the 'plunger' so that the syringe may be sealed after use.
- Following the instructions on the back of the blister card, dispense equal volumes of resin and hardener onto a clean disposable surface. Mix well for 30 seconds, by stirring and folding, with the plastic palette knife provided. It is important to ensure a thorough mix.
- Carefully reseal the syringe with the cap as soon as possible. Apply the mixed adhesive to both surfaces of the joint and assemble carefully. A layer of adhesive 0.05 to 0.10 mm thick will normally impart the greatest lap shear strength to the joint.
- Keep the joint supported until set. A rubber band or sticky tape is ideal An approximate guide to support and handling times at room temperature is given below:

5 minutes, approximately at 23°C (RT)

Support time: 20-30 minutes at RT

Handling time: 1-2 Hours.

Setting times may be shorter in hot weather. In cold conditions the rate of curing of the mixed adhesive may be slowed down significantly and weak joints may result. For best results use between 20°C and 25°C.

For a perfect finish carefully remove any excess adhesive with a sharp knife before the adhesive has fully hardened.

#### **CLEANING**

Uncured resin/hardener mixtures can be cleaned from tools using cellulose thinners or acetone. Solvents must always be handled with due care as they may be hazardous or flammable. Methoxypropanol is an alternative solvent which significantly reduces the flammability hazard. Please note that solvents may attack some rubbers, plastics, painted surfaces, fabrics, etc..

- Bear this in mind if intending to use solvent to remove excess adhesive, and carry out a preliminary test first.
- Cured adhesive residues can usually be dissolved from tools by soaking in commercial paint stripper. Refer to the paint stripper manufacturer's instructions for use and safe handling.
- The adhesive may be removed from the skin using a suitable proprietary hand cleaner. Contact with the skin should however be avoided. Do not use solvents in contact with the skin. Always open and use adhesive products over a protected surface, and avoid contact with clothing.

**PACKAGING** Code: 80808 1x6 Blister

HEALTH AND SAFETY Available separately in files named as the packaging code above.

SHELF LIFE: 3 years if stored as directed below

STORAGE & TRANSPORTATION: Store under dry conditions between 5°C and 25°C.

#### SPECIAL INFORMATION

- Thorough mixing is the key to getting a good cured product. Simply stirring leaves unmixed materials at the margins. Always fold in the edges then re-stir.
- Cured adhesive may yellow if exposed to sunlight for long periods.

## TYPICAL ADHESIVE CHARACTERISTICS

**RESIN HARDENER** Physical form: Liquid Liquid Chemical type: **Epoxy Resin** Formulated Polyamine Viscosity: Slow flowing Slow flowing Solids content: 100% 100% Colourless Pale yellow Colour: Density (SG): 1.17 1.16 3082 UN Class: # 9 Pack Group: III

## TYPICAL PERFORMANCE CHARACTERISTICS

Colour mixed: Pale yellow

1.16  $^{\circ}$  -50 $^{\circ}$ C to +65 $^{\circ}$ C depending on conditions of use Cured Density (SG):

Temperature: Not intended for constant immersion Water:

Oil & Petrol: Good resistance. Chemicals: Good resistance.

Sandability: Sandable when set. Please wear dust mask. Paintability: Good, but confirm by test. Fine sanding helps.

## Sales and Technical contacts at Bostik Findley:

Telephone Email addresses Facsimile 01785 272700 01785 241818 RVICE@BOSTIKFINDLEY.COM Sales Technical advice 01785 272764 01785 272867 TECHNICAL.SERVICE@BOSTIKFINDLEY.COM Data & COSHH (MSDS) sheets 01785 272827

<sup>®</sup>ARALDITE is a registered trademark of Huntsman.

006-02

This Product Data Sheet covers just one of a large range of products supplied by Bostik Findley Limited. Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This Product Data Sheet supersedes all previous technical information on this product, and users of it are cautioned to ensure that it is the current issue. Destroy all previous Product Data Sheets, and if any doubt, contact Bostik Findley Limited, quoting the code number in the top right hand corner on the front of this document. This leaflet is for general guidance only and may contain inappropriate information under particular conditions of use. The company cannot accept any responsibility for loss or damage that may result from the use of this info

Bostik Findley Limited, Common Road, Stafford, England. Tel: +44 (0)1785 272727 Fax: +44 (0)116 253 1943