



Acer recommends Windows 10 Pro.



## Veriton X



Faster Data Transit  
2666 MHz



Data Access



Acer Office Manager



Acer Control Center



ProShield Security



TPM





Easy-swap  
Expansion Bay



Power On By Monitor

**SPECIFICATIONS** **Veriton** **X2665G**



<b>Product views</b>	1. Power button 2. One button recovery 3. Optical media drive 4. Two USB 3.1 Gen 1 ports 5. Status LEDs	6. Headphone/speaker jack 7. Microphone-in jack 8. Two USB 3.1 Gen 2 ports 9. Audio jacks 10. VGA port	11. DisplayPort™ 12. HDMI® port 13. Four USB 2.0 ports 14. PS/2 ports 15. COM (Serial) port	16. Ethernet (RJ-45) port 17. Power connector
<b>Operating system<sup>1,2</sup></b>	Windows 10 Pro 64-bit Windows 10 Home 64-bit Endless OS			
<b>CPU and chipset<sup>1</sup></b>	9th Generation Intel® Core™ i9 processor, Intel® UHD Graphics 630 9th Generation Intel® Core™ i7 processor, Intel® UHD Graphics 630 9th Generation Intel® Core™ i5 processor, Intel® UHD Graphics 630 9th Generation Intel® Core™ i3 processor, Intel® UHD Graphics 630 Intel® Pentium® Gold processor, Intel® UHD Graphics 630 / 610 Intel® Celeron® processor, Intel® UHD Graphics 610 Chipset: Intel® B365 Express Chipset			
<b>Memory<sup>1,3,4</sup></b>	16 GB / 8 GB / 4 GB DDR4 2666 MHz UDIMM Up to 32 GB of Dual-channel DDR4 2666 MHz			
<b>Storage<sup>1,5</sup></b>	<b>Hard disk drive</b> • 500 GB 2.5-inch 5400 RPM • 1 TB 2.5-inch 5400 RPM, 7 mm high • 2 TB / 1 TB / 500 GB 3.5-inch 7200 RPM • 512 GB / 256 GB / 128 GB M.2 2280 PCI-E SSD • Intel® Optane Memory 32 GB / 16 GB PCIe M.2 2280			
<b>Optical media drive</b>	8X DVD-RW drive, 9.0 mm slim, tray-load, M-DISC Ready™			
<b>Graphics<sup>6</sup></b>	NVIDIA® GeForce® GT 720 with 2 GB of DDR3 AMD Radeon™ R7 430, 4 GB GDDR5			
<b>Audio</b>	Integrated high-definition sound			
<b>Communication</b>	<b>WLAN</b> Wireless LAN Intel® 802.11ac Bluetooth FM 9260.NG.WG.NV THP2 M.2 2x2AC MU-MIMO/160Mhz + BT5 2230 non-vPro <b>LAN</b> Gigabit Ethernet			
<b>Expansion slot(s)</b>	PCIe x16 slot: 2 (one slot supports x4 signal) PCIe x1 slot: 1 PCI slot: 1		M.2 slot (for SSD): 1 M.2 slot (for WLAN): 1	
<b>Windows Desktop Apps<sup>7</sup></b>	• Acer Office Manager • Acer Control Center		• Acer ProShield	
<b>Commercial features</b>	One-button recovery (OBR) Kensington lock slot 100% solid capacitors Hard drive password protection (via BIOS)		PXE (Preboot eExecution Environment) WOL (Wake On Lan) ASF (Alert Standard Format) 2.0 Intrusion alert (via BIOS)	
<b>Commercial selected options<sup>8</sup></b>	Parallel (printer) port COM (Series) port SD card reader module TPM v2.0 (Trusted Platform Module)		DisplayPort™-to-DVI adapter Dual-channel memory support Internal speaker Dust filter	
<b>Dimensions</b>	102 (W) x 305.08 (D) x 330 (H) mm (4.02 x 12.01 x 12.99 inches)			
<b>Power supply and adapter</b>	<b>Power supply</b> 250 W PFC, auto-sensing, 80PLUS® Platinum, TFX 180 W PFC, auto-sensing, 80PLUS® Platinum, TFX 180 W PFC, auto-sensing, 80PLUS® Bronze, TFX			
<b>System compliance</b>	RoHS, DMI, GS, ENERGY STAR®, PC2001			
<b>Options and accessories</b>	USB keyboard and mouse PS/2 keyboard and mouse			
<b>Certification</b>	BSMI, CE, FCC, CB			

1. Specifications vary depending on model.  
2. 64-bit software is required to enjoy the advantages of 64-bit processing.  
3. A 64-bit operating system is required to enjoy the ultimate performance of 4 GB or higher memory.  
4. Memory speed may vary, depending on the CPU, chipset or memory fitted.  
5. 1 GB is 1 billion bytes. Actual formatted capacity is less and may vary depending on preloaded materials and operating environment. Recovery Management uses a portion of the stated hard disk capacity as dedicated backup space.  
6. Total available graphics memory comprises dedicated video memory, system memory, and shared system memory. This figure will vary depending on system memory, installed drivers, BIOS settings and other factors.  
7. Bundled software may vary depending on hardware configuration, OS and regional availability.  
8. For systems with a dual-channel configuration, the two memory modules inserted must be identical, including raw card, size, type, and speed.

In a continuing effort to improve the quality of our products, information in this document is subject to change without notice. Images shown are only representations of some of the configurations available for this model. Availability may vary depending on region. As a phenomenon known to thin-film transistors (TFTs), liquid crystal displays (LCDs) commonly exhibit a small number of discoloration dots, as so-called "non-conforming pixels." This phenomenon is a limitation of TFT LCD technology, not a product defect, and as such is not covered by Acer's warranty.  
© 2019. All rights reserved.  
Microsoft and Windows are registered trademarks of Microsoft Corporation.  
Ultrabook, Celeron, Celeron Inside, Core Inside, Intel, Intel Logo, Intel Atom, Intel Atom Inside, Intel Core, Intel Inside, Intel Inside Logo, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, vPro Inside, Xeon, Xeon Phi, Xeon Inside, and Intel Optane are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries.

**About Acer**  
Founded in 1976, Acer is now one of the world's top ICT companies and has a presence in over 160 countries. As Acer looks into the future, it is focused on enabling a world where hardware, software and services will fuse with one another to open up new possibilities for consumers and businesses alike. From service-oriented technologies to the Internet of Things to gaming and virtual reality, Acer's 7,000+ employees are dedicated to the research, design, marketing, sale, and support of products and solutions that break barriers between people and technology. Please visit [www.acer.com](http://www.acer.com) for more information.