



Wiha. Premium Tools
for Professionals.

Wiha Ceramic Screwdriver. The Non-static Adjustment Tool for Clean Rooms.




With blade made of special ceramic material for working on high frequency applications. Rotating cap and rapid rotating zone ensure optimum handling.



The Wiha Ceramic precision screwdrivers with blades made of high-tech zirconium ceramic are the perfect tools for all applications in clean rooms and for delicate electrostatic components. In these areas there are high requirements in terms of eddy-current losses. The ceramic blades and handles are completely anti-magnetic and anti-static. This is a fundamental requirement for working with highly sensitive components, such as capacitors, solenoids and various resistances.

The ceramic blades are resistant to mechanical wear, acid corrosion and thermal shock stress. Wiha Ceramic screwdrivers are available with slotted and Phillips tips, as well as in sets.



The Product Advantages:

- Ideal for adjusting electrical components
- Suitable for working in clean rooms
- High thermal and electrical insulation
- Anti-static and anti-magnetic handle and blade
- Rotating cap for easy working
- Resistant to mechanical wear, thermal shock stress and acidic corrosion



Wiha. Premium Tools
for Professionals.

Wiha Ceramic. The Non-static Adjustment Tool for Clean Rooms.

For Slotted & Phillips Screws.



270

Slotted Screwdriver.

With high thermal and electrical insulation.

Handle: Wiha Precision handle with rotating cap, anti-static/anti-magnetic.

Blade: Made of high-quality special ceramic, anti-static/anti-magnetic.

Application: Specially designed for tuning and adjusting high frequency devices, suited to cleanrooms.

| Order-No. | Ø | Length | Blade Length | Blade Width | Blade Thickness | Blade Height | Blade Depth |
|-----------|-----|--------|--------------|-------------|-----------------|--------------|-------------|
| 02163 4 | 0.9 | 15 | 0.35 | 94.5 | 1.75 | 12.5 | 10 |
| 02164 1 | 1.3 | 15 | 0.35 | 94.5 | 1.75 | 12.5 | 10 |
| 02167 2 | 1.8 | 15 | 0.35 | 94.5 | 1.75 | 12.5 | 10 |
| 02168 9 | 2.6 | 15 | 0.35 | 94.5 | 2.6 | 12.5 | 10 |



271

Phillips Screwdriver.

With high thermal and electrical insulation.

Handle: Wiha Precision handle with rotating cap, anti-static/anti-magnetic.

Blade: Made of high-quality special ceramic, anti-static/anti-magnetic.

Application: Specially designed for tuning and adjusting high frequency devices, suited to cleanrooms.

| Order-No. | Ø | Length | Blade Length | Blade Width | Blade Thickness | Blade Height | Blade Depth |
|-----------|---|--------|--------------|-------------|-----------------|--------------|-------------|
| 02169 6 | 0 | 15 | 94.5 | 2.6 | 12.5 | 10 | |

Ceramic Screwdriver Set.



609-780

270 HK 3

Slotted/Phillips Screwdriver Set, 3-pcs.

With high thermal and electrical insulation.

Handle: Wiha Precision handle with rotating cap, anti-static/anti-magnetic.

Blade: Made of high-quality special ceramic, anti-static/anti-magnetic.

Application: Specially designed for tuning and adjusting high frequency devices, suited to cleanrooms.

Extra: Packed in durable plastic box.

| Order-No. | Series | Blade Length | Blade Width | Blade Thickness | Blade Height | Blade Depth |
|-----------|--------|--------------|-------------|-----------------|--------------|-------------|
| 02171 9 | | | | | | 1 |
| | Ø: 270 | 0.9 | 2.6 | | | |
| | ⊕ 271 | PH 0 | | | | |