



#### TECHNICAL INFORMATION

Input Power:	AC/DC:12V
Unit Color:	Black+Silver
Body Type:	Stainless Steel
Dimmable:	No
Rated Load:	Max 20W
Dimension:	Ø87x128mm
Type:	Three Window

#### UNDERGROUND FITTINGS MR16

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 8566 - 2689

[View more details](#)

## UNDERGROUND FITTINGS

AC/DC 12V

MR16

Compatible with any standard MR16 lamp.

\*Lamps are not included



IP67  
RATING



3 YEAR  
WARRANTY

#### FEATURES

- Perfect replacement for traditional underground fittings
- Strong and sturdy Stainless Steel body
- Ingress protection IP67
- Easy to install and requires little maintenance
- Compatible with MR16 holder type (Fitting only - light not included)
- Suitable for pathways, driveways, tree uplighting etc.
- Recommended daily usage: 10 - 12 hours \*Exceeding recommended daily usage will void warranty



#### PACKAGING

Gross Weight (Kgs): 0.766  
Unit CBM: 0.0015  
Dimension: Ø87x128mm

#### MASTER BOX PACKAGING

Box Qty: 12  
Qty Per Pallet: 600  
Length (Box) mm: 100  
Width (Box) mm: 100  
Height (Box) mm: 150

#### LISTING DETAILS

Commodity Code: 9405109890  
EanCode: 3800157644532