


Made of tungsten for optimum lifetime. For drilling glass, semi-precious stones, porcelain,

ceramics, marble and other hard stones. With ideal cutting angle of 6°. Shaft of 3mm.




# 1,0 u. 1,2 0,6 u. 0,8 NO 28 320 NO 28 321

NO 28 255

Tungsten carbide milling drills (Speardrill) For drilling, milling and cutting fibre glass or PERTINAX circuit boards. Also for drilling pearls and similar. Shaft 2.35mm.

Diamond twist drills With natural diamond dust for drilling precious stones (pearls, coral, turquoise). Shafts 2.35mm.



cast iron, steel,

Hard microdrills

#### Silicon carbide grinding bits

Fine particles of consistent hardness for engraving and frosting of glass, ceramics and stellites. Also for use on cast steel, cast iron and other hard steels. All shafts 2.35mm.

#### Diamond grinding bits


With consistently even coating of diamond dust. Shafts of 2.35mm made from stainless steel. Used for grinding and engraving hard materials: steel (even chrome-cobalt alloy), glass, ceramics, porcelain, plastics.



expectancy. All shafts 2.35 or 3.0mm. For use on


### Tungsten carbide millers

Made of wear-resistant tungsten. Used for vibration-free milling of high accuracy dimensions. It is advisable to secure workpieces well, avoiding accidents. For technical work on extremely hard materials: chrome-cobalt alloy, steel, non-ferrous metals, plastics. May be used for engraving and milling of PC cards.



NO 28 818

unbreakable, making it usable to remove and even wood and plastics.



NO 28 830

## Metal cutting blades

Spring steel, 0.1mm thick. For nonferrous metals, plastic and wood. Shaft 2.35mm





NO 28 840

NO 28 842

## Diamond cutting disc

Only 0.6mm thick. For cutting very hard materials such as steel, porcelain, fibreglass, non-ferrous metals. Arbor 2.35mm.