

Indicator Lights (Neon, LED and Filament Lamp)



UL file E63363

CSA file LR29381

Colours and voltages:

Neon	Red, Amber, Green, Clear 100/130V (marked 110V), 200/250V (marked 230V)
LED	Red, Yellow, Green 2.0/2.2V Resistors for other voltages available
Filament lamp	Red, Amber, Green, (Clear & Blue check availability) 6V, 12/14V, 24/28V

To create a catalogue number:







Refer to the 2 columns below (terminal and type)

Then state:

Lens colour, voltage and whether neon, LED or filament lamp

TERM	TYPE	PANEL & °C
C 6.3	(C) 0145 AA S D N F S UL	Ø 5.8 3.0max page 66
L W	(L) 1041 00 Chrome bezel UL	Ø 6.3 6.3max page 66
L W	(L) 1045 00 Chrome bezel available S D N F S UL	Ø 6.3 10.0max page 66
L W	(L) 0245 00 Chrome bezel available S D N F S UL	Ø 7.1 6.3max page 66
L	L 2950 00 Chrome bezel available S D N F S UL SF	Ø 8.0 0.8-1.6 page 66
L C 6.3	(L) 0195 BB S D N F KEMA EUR S UL	Ø 8.0 0.8-3.0 page 66

DIMENSIONS (mm)



Indicator Lights (Neon, LED and Filament Lamp)



UL file E63363

CSA file LR29381

Colours and voltages:







Neon	Red, Amber, Green, Clear 100/130V (marked 110V), 200/250V (marked 230V)
LED	Red, Yellow, Green 2.0/2.2V Resistors for other voltages available
Filament lamp	Red, Amber, Green, (Clear & Blue check availability) 6V, 12/14V, 24/28V

To create a catalogue number:

Refer to the 2 columns below (terminal and type)

Then state:

Lens colour, voltage and whether neon, LED or filament lamp

TERM	TYPE	PANEL & °C
L	L 2951 00 Chrome bezel available 	8.0 0.8-1.6 page 66
L	(H) 0568 A(*) Deep lens profile 	8.0 0.8-3.5 page 66
K 2.8		
H 4.8		
L	(H) 0568 B(*) Shallow lens profile 	8.0 0.8-3.5 page 66
K 2.8		
H 4.8		
L	(L) 0569 AW 	9.0 0.8-2.5 Call factory
L	(C) 0273 00 	9.0 2.0 max page 66
K 2.8		
H 4.8		
C 6.3		
L	(C) 0278 00 	9.0 2.0 max page 66
K 2.8		
H 4.8		
C 6.3		

DIMENSIONS (mm)

