

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0761551103**
Status: **Active**
Overview: Impact Backplane Connector and Cable Assembly System
Description: Impact 100 Ohm 4 Pair Vertical Backplane Header, Unguided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free

Documents:

3D Model	Application Specification AS-76060-9999-001 (PDF)
3D Model (PDF)	Packaging Specification PK-70873-7701-001 (PDF)
Drawing (PDF)	Test Summary TS-76160-0001-001 (PDF)
Product Specification PS-76060-999-001 (PDF)	Symbol Footprint Data SYM-76155-1103 (PDF)
Application Specification AS-76060-990-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-76060-994-001 (PDF)	

Agency Certification


UL E29179

General

Product Family	Backplane Connectors
Series	<u>76155</u>
Application	Conventional
Application Tooling Documents	TM-622018799
Component Type	PCB Header
Overview	<u>Impact Backplane Connector and Cable Assembly System</u>
Product Name	Impact
UPC	883906417079

Physical

Circuits (Loaded)	120
Circuits (maximum)	120
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.555/g
Number of Columns	10
Number of Pairs	4
Number of Rows	12
Orientation	Vertical
PC Tail Length	1.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Packaging Type	Tray
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Polarized to PCB	No
Stackable	No



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

76155 Series

Mates With

76160 Impact 100 Ohm Daughtercard

Use With

75234 Backplane Free Standing Guide Pin

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Backplane Insertion Tool for Signal Contact	<u>621005800</u>
---	------------------

Backplane Header Removal Tool for GbX U-Series, GbX I-Trac, Impact, or Z-PACK TinMan	<u>621009610</u>
--	------------------

Temperature Range - Operating
Termination Interface: Style

-55° to +85°C
Through Hole - Compliant Pin

Backplane Module 622018640
Installation Press-In
Tool

Electrical

Current - Maximum per Contact 0.75A
Data Rate 25.0 Gbps
Impedance 100Ω
Shield Type N/A
Shielded No
Voltage - Maximum 30V AC (RMS)/DC

Solder Process Data

Lead-free Process Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification AS-76060-990-001, AS-76060-994-001,
AS-76060-9999-001
Packaging Specification PK-70873-7701-001
Product Specification PS-76060-999-001
Sales Drawing SD-76155-001-001
Symbol/Footprint Data SYM-76155-1103
Test Summary TS-76160-0001-001

This document was generated on 07/17/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION