

Slide Switches

Miniature

multicomp PRO

**RoHS
Compliant**



Specifications


Max. Contact Rating	: 0.4 (VA) maximum at 20V maximum (AC or DC)
Mechanical Life	: 20,000 cycles
Max. Initial Contact Resistance	: 50mΩ
Min. Insulation Resistance	: 1,000MΩ
Dielectric Strength	: 1,000V RMS at sea level
Operating Temperature	: -40°C to +80°C
Minimum Load	: 10mA, 50mV
Breaking Capacity	: 100mA, 30V DC with resistive load

Materials


Case	: Nylon, white
Housing	: Nylon, black
Actuator	: Nylon, black
Contacts / Terminals	: Copper alloy, with gold plated

Pole Option

M1RE




SPDT




PCB Mounting




M2RE



DPDT



PCB Mounting



Dimensions : Millimetres (Inches)

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Slide Switches Miniature

multicomp PRO

Soldering Process


Manual Soldering : Use soldering iron of 30 W, controlled at 350°C approximately 5 seconds while applying solder

Wave Soldering:

Recommended Soldering Temperature : 260 ±5°C
Duration of solder immersion : 5 ±1 seconds (PCB is 1.6 mm in thickness)

Soldering : Vapour phase

Temperature Profile		
Zone	Room Temperature (°C)	Time (Seconds)
Pre-heat (A)	150°C	Minimum 120
Soak (B)	180°C to 200°C	Minimum 150
Peak (C)	200°C to 235°C	Minimum 30
Peak (D)	235°C to 260°C	Minimum 40
Peak (E)	260°C	Maximum 10



Specification Table

Number of Poles	Switch Function			Connected Terminals			Schematic	Model Number
	Position 1	Position 2	Position 3	Position 1	Position 2	Position 3		
SP	On	None	On	2 - 1	Open	2 - 3		6MS1
DP				2 - 1, 5 - 4		2 - 3, 5 - 6		6MD1

Part Number Table

Description	Part Number
Switch, Slide, SPDT, On-On	6MS1S2M1RE
Switch, Slide, DPDT, On-On	6MD1S2M2RE
Switch, Slide, SPDT, On-On	6MS1S4M1RE
Switch, Slide, DPDT, On-On	6MD1S4M2RE
Switch, Slide, SPDT, R / A, On-On	6MS1S3M1RE
Switch, Slide, DPDT, R / A, On-On	6MD1S3M2RE

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO