



Main

Range	Acti9
Product name	Acti9 iID
Product or component type	Residual current circuit breaker (RCCB)
Device short name	IID
Device application	Photovoltaic 3P speed drive Lift
Poles description	4P
Neutral position	Left
[In] rated current	80 A
Network type	AC
Earth-leakage sensitivity	500 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type B-SI
Quality labels	VDE NF IMQ KEMA

Complementary

Device location in system	Outgoer Group incomer
Network frequency	50 Hz
[Ue] rated operational voltage	400 V AC 50 Hz
Rated breaking and making capacity	I _{dm} 1500 A I _m 1500 A
Rated conditional short-circuit current	10 kA
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON/OFF indication LED (green)presence of voltage:

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

	Trip indicator
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	88 mm
Width	72 mm
Depth	79 mm
Net weight	415 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Locking options description	Padlocking device
Connections - terminals	Double terminal front 1...35 mm ² rigid Double terminal front 1...25 mm ² flexible Double terminal front 1...25 mm ² flexible with ferrule Double terminal back 1...25 mm ² rigid Double terminal back 1...16 mm ² flexible Double terminal back 1...16 mm ² flexible with ferrule
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom

Environment

Standards	IEC 61008-2-1 IEC/EN 62423 EN 61008-2-1
Product certifications	CCC KC
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
IK degree of protection	IK05
Pollution degree	3
Overvoltage category	IV
Electromagnetic compatibility	8/20 µs impulse withstand, 3 kA conforming to EN/IEC 61008-1
Operating altitude	0...2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	427 g
Package 1 Height	7.5 cm
Package 1 width	8.5 cm
Package 1 Length	10 cm
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Weight	11.976 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins