



Main

Range	PowerTag
Product or component type	Input and output module
Device short name	PowerTag C IO 230V
Product name	PowerTag Control
Product name	Acti9 PowerTag Link C Wiser IP module Acti9 PowerTag Link Acti9 PowerTag Link HD
Range compatibility	impulse relay contactor iACTs remote indication auxiliary iATLs remote indication auxiliary

Complementary

[Us] rated supply voltage	230 V AC (+/- 20 %)
Network frequency	50/60 Hz
Power consumption in VA	2 VA
Digital input number	1
Input type	Dry contact 230 V AC 2 mA
Voltage state 1 guaranteed	≥ 164 V for digital input
Voltage state 0 guaranteed	≤ 40 V for digital input
Current state 1 guaranteed	≥ 2 mA (digital input)
Current state 0 guaranteed	≤ 0.5 mA (digital input)
Digital output number	1
Output type	Dry contact 230 V 0.01...2 A AC
Discrete output type	Configurable relay logic
Output function	NO/NC programmable
Mechanical durability	100000 cycles for output
Mounting mode	Clip-on
Mounting support	DIN rail
Local signalling	Green, orange and red LED for product status
Impulse duration	300 ms by default - 0 ms, + 300 ms

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Time between 2 impulse	100 ms minimum - tolerance: - 0 ms, + 300 ms
Colour	White (RAL 9003)
9 mm pitches	2
Height	85 mm
Width	18 mm
Material	PA6 GF30
Depth	62 mm
Net weight	80 g
Connections - terminals	Tunnel type terminals (top) - 1 cable(s) 1...16 mm ² (AWG 18...AWG 16) - rigid Tunnel type terminals (top) - 1 cable(s) 0.5...10 mm ² (AWG 21...AWG 8) - flexible Tunnel type terminals (bottom) - 1 cable(s) 1...6 mm ² (AWG 18...AWG 10) - rigid Tunnel type terminals (bottom) - 1 cable(s) 0.5...4 mm ² (AWG 21...AWG 12) - flexible Tunnel type terminals (bottom) - 1 cable(s) 0.5...4 mm ² (AWG 21...AWG 12) - flexible with ferrule Tunnel type terminals (bottom) - 2 cable(s) 1.5...2.5 mm ² (AWG 16...AWG 14) - rigid Tunnel type terminals (bottom) - 2 cable(s) 1.5...2.5 mm ² (AWG 16...AWG 14) - flexible
Wire stripping length	14 mm for top connection 9 mm for bottom connection
Tightening torque	Power supply: 2 N.m top Digital input/output: 1 N.m bottom
Standards	EN/IEC 61010-1 ETSI EN 300 328 EN/IEC 62479 ETSI EN 301 489-17 ETSI EN 301 489-1 EN/IEC 61010-2-201 EN/IEC 61326-1

Environment

IP degree of protection	IP20 casing: conforming to IEC 60529 IP40 front face: conforming to IEC 60529
Pollution degree	3
Overvoltage category	III conforming to IEC 61010-1
IK degree of protection	IK05
Relative humidity	0...93 % at 40 °C conforming to IEC 60068-2-78
Operating altitude	0...2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C
Fire resistance	960 °C / 30 s conforming to UL 94 V0

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	116 g
Package 1 Height	3 cm
Package 1 width	8 cm
Package 1 Length	11.5 cm
Unit Type of Package 2	S03
Number of Units in Package 2	80
Package 2 Weight	9.65 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P06
Number of Units in Package 3	640
Package 3 Weight	80.24 kg
Package 3 Height	80 cm
Package 3 width	80 cm

Package 3 Length	60 cm
------------------	-------

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
