



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 14

LOCTITE SF 734 AERO known as Loctite 734

SDS No. : 179516
V004.0

Revision: 02.10.2018

printing date: 14.07.2020

Replaces version from: 09.07.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE SF 734 AERO known as Loctite 734

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
activator

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Adhesives
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000
Fax-no.: +44 (1442) 278071

ua-productsafety.uk@henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Flammable aerosols	Category 1
H222 Extremely flammable aerosol.	
H229 Pressurised container: May burst if heated.	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	
Specific target organ toxicity - single exposure	Category 3
H336 May cause drowsiness or dizziness.	
Target organ: Central Nervous System	

2.2. Label elements

Label elements (CLP):

Hazard pictogram:**Contains**

Acetone

Signal word:

Danger

Hazard statement:

H222 Extremely flammable aerosol.
 H229 Pressurised container: May burst if heated.
 H319 Causes serious eye irritation.
 H336 May cause drowsiness or dizziness.

Supplemental information

EUH066 Repeated exposure may cause skin dryness or cracking.

Precautionary statement:

P251 Do not pierce or burn, even after use.
 P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
 P211 Do not spray on an open flame or other ignition source.
 P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.
 No smoking.
 P102 Keep out of reach of children.

**Precautionary statement:
Prevention**

P261 Avoid breathing spray.
 P280 Wear protective gloves/protective clothing.

**Precautionary statement:
Response**

P337+P313 If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

SECTION 3: Composition/information on ingredients**3.2. Mixtures****General chemical description:**

Solvent based activator.

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Acetone 67-64-1	200-662-2 01-2119471330-49	75- 100 %	Flam. Liq. 2 H225 Eye Irrit. 2 H319 STOT SE 3 H336
Propane 74-98-6	200-827-9 01-2119486944-21	2,5- < 10 %	Flam. Gas 1 H220 Press. Gas
Butanal react. prod. with butylamine 68411-19-8	270-108-2	2,5- < 10 %	Acute Tox. 4; Oral H302 Acute Tox. 4; Dermal H312 Acute Tox. 4; Inhalation H332
Butane, n- (< 0.1 % butadiene) 106-97-8	203-448-7 01-2119474691-32	1- < 2,5 %	Flam. Gas 1 H220 Press. Gas
Isobutane 75-28-5	200-857-2 01-2119485395-27	0,1- < 1 %	Flam. Gas 1 H220 Press. Gas

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.
Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.
Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Vapors may cause drowsiness and dizziness.

EYE: Irritation, conjunctivitis.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

None known

5.2. Special hazards arising from the substance or mixture

Oxides of carbon, oxides of nitrogen, irritating organic vapors.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid skin and eye contact.

Ensure adequate ventilation.

See advice in section 8

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

Dispose of contaminated material as waste according to Section 13.

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Use only in well-ventilated areas.

Vapours should be extracted to avoid inhalation.

Keep away from sources of ignition - no smoking.

Avoid skin and eye contact.

See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.

Keep away from heat and direct sunlight.

7.3. Specific end use(s)

activator

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Acetone 67-64-1 [ACETONE]	1.500	3.620	Short Term Exposure Limit (STEL):		EH40 WEL
Acetone 67-64-1 [ACETONE]	500	1.210	Time Weighted Average (TWA):		EH40 WEL
Acetone 67-64-1 [ACETONE]	500	1.210	Time Weighted Average (TWA):	Indicative	ECLTV
Butane 106-97-8 [BUTANE]	750	1.810	Short Term Exposure Limit (STEL):		EH40 WEL
Butane 106-97-8 [BUTANE]	600	1.450	Time Weighted Average (TWA):		EH40 WEL

Occupational Exposure Limits

Valid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Acetone 67-64-1 [ACETONE]	500	1.210	Time Weighted Average (TWA):	Indicative OELV	IR_OEL
Acetone 67-64-1 [ACETONE]	500	1.210	Time Weighted Average (TWA):	Indicative	ECLTV
Propane 74-98-6 [PROPANE]	1.000		Time Weighted Average (TWA):		IR_OEL
Butane 106-97-8 [BUTANE]	1.000		Time Weighted Average (TWA):		IR_OEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Acetone 67-64-1	aqua (intermittent releases)		21 mg/l				
Acetone 67-64-1	sewage treatment plant (STP)		100 mg/l				
Acetone 67-64-1	sediment (freshwater)				30,4 mg/kg		
Acetone 67-64-1	sediment (marine water)				3,04 mg/kg		
Acetone 67-64-1	Soil				29,5 mg/kg		
Acetone 67-64-1	aqua (freshwater)		10,6 mg/l				
Acetone 67-64-1	aqua (marine water)		1,06 mg/l				

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Acetone 67-64-1	Workers	Inhalation	Acute/short term exposure - local effects		2420 mg/m ³	
Acetone 67-64-1	Workers	dermal	Long term exposure - systemic effects		186 mg/kg	
Acetone 67-64-1	Workers	Inhalation	Long term exposure - systemic effects		1210 mg/m ³	
Acetone 67-64-1	General population	dermal	Long term exposure - systemic effects		62 mg/kg	
Acetone 67-64-1	General population	Inhalation	Long term exposure - systemic effects		200 mg/m ³	
Acetone 67-64-1	General population	oral	Long term exposure - systemic effects		62 mg/kg	

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Use only in well-ventilated areas.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

The use of chemical resistant gloves such as Neoprene or Natural Rubber is recommended

Please note that in practice the working life of chemical resistant gloves may be considerably reduced as a result of many influencing factors (e.g. temperature). Suitable risk assessment should be carried out by the end user. If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Protective eye equipment should conform to EN166.

Skin protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance

aerosol

Amber

Odor

pungent

Odour threshold

No data available / Not applicable

pH	Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	-44,5 °C (-48.1 °F)
Flash point	Not applicable to aerosols.
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure (20 °C (68 °F))	8300 mbar
Relative vapour density:	Heavier than air
Density (ρ)	0,8 g/cm ³
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Not miscible
Solubility (qualitative) (Solvent: Acetone)	Miscible
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Reaction with strong acids.
Reacts with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

Irritating organic vapours.

SECTION 11: Toxicological information

General toxicological information:

Prolonged or repeated contact may cause skin irritation.

11.1. Information on toxicological effects

Acute oral toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Acetone 67-64-1	LD50	5.800 mg/kg	rat	not specified

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Acetone 67-64-1	LD50	> 15.688 mg/kg	rabbit	Draize Test

Acute inhalative toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Test atmosphere	Exposure time	Species	Method
Acetone 67-64-1	LC50	76 mg/l		4 h	rat	not specified
Propane 74-98-6	LC50	> 800000 ppm	gas	15 min	rat	not specified
Butane, n- (< 0.1 % butadiene) 106-97-8	LC50	274200 ppm	gas	4 h	rat	not specified
Isobutane 75-28-5	LC50	260200 ppm	gas	4 h	mouse	not specified

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Acetone 67-64-1	not irritating		guinea pig	not specified

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Acetone 67-64-1	irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
Acetone 67-64-1	not sensitising	Guinea pig maximisation test	guinea pig	not specified

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Acetone 67-64-1	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Acetone 67-64-1	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Acetone 67-64-1	negative	mammalian cell gene mutation assay	without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
Propane 74-98-6	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Propane 74-98-6	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Butane, n- (< 0.1 % butadiene) 106-97-8	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Butane, n- (< 0.1 % butadiene) 106-97-8	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Isobutane 75-28-5	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Isobutane 75-28-5	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Acetone 67-64-1	negative	oral: drinking water		mouse	not specified
Propane 74-98-6	negative			Drosophila melanogaster	not specified
Butane, n- (< 0.1 % butadiene) 106-97-8	negative			Drosophila melanogaster	not specified
Isobutane 75-28-5	negative			Drosophila melanogaster	not specified

Carcinogenicity

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Sex	Method
Acetone 67-64-1	not carcinogenic	dermal	424 d 3 times per week	mouse	female	not specified

Reproductive toxicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
Butane, n- (< 0.1 % butadiene) 106-97-8	NOAEL P 21,4 mg/l NOAEL F1 21,4 mg/l			rat	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)

STOT-single exposure:

No data available.

STOT-repeated exposure::

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
Acetone 67-64-1	NOAEL 900 mg/kg	oral: drinking water	13 w daily	rat	OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity in Rodents)
Propane 74-98-6		inhalation: gas	28 d	rat	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)
Butane, n- (< 0.1 % butadiene) 106-97-8		inhalation: gas	28 d	rat	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)
Isobutane 75-28-5		inhalation: gas	28 d	rat	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)

Aspiration hazard:

No data available.

SECTION 12: Ecological information

General ecological information:

Do not empty into drains / surface water / ground water.

12.1. Toxicity

Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Acetone 67-64-1	LC50	8.120 mg/l	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Butane, n- (< 0.1 % butadiene) 106-97-8	LC50	27,98 mg/l	96 h		not specified

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Acetone 67-64-1	EC50	8.800 mg/l	48 h	Daphnia pulex	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Butane, n- (< 0.1 % butadiene) 106-97-8	EC50	14,22 mg/l	48 h		not specified

Chronic toxicity to aquatic invertebrates

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Acetone 67-64-1	NOEC	2.212 mg/l	28 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Acetone 67-64-1	NOEC	530 mg/l	8 d	Microcystis aeruginosa	DIN 38412-09
Butane, n- (< 0.1 % butadiene) 106-97-8	EC50	7,71 mg/l	96 h		not specified
Isobutane 75-28-5	EC50	7,71 mg/l	96 h		not specified

Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Acetone 67-64-1	EC10	1.000 mg/l	30 min	Pseudomonas putida	DIN 38412, part 27 (Bacterial oxygen consumption test)

12.2. Persistence and degradability

No data available.

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
Acetone 67-64-1	readily biodegradable	aerobic	81 - 92 %	30 d	EU Method C.4-E (Determination of the "Ready" Biodegradability Closed Bottle Test)

12.3. Bioaccumulative potential

No data available.

No substance data available.

12.4. Mobility in soil

The product evaporates readily.

Hazardous substances CAS-No.	LogPow	Temperature	Method
Acetone 67-64-1	-0,24		OECD Guideline 107 (Partition Coefficient (n-octanol / water), Shake Flask Method)
Isobutane 75-28-5	2,88	20 °C	OECD Guideline 107 (Partition Coefficient (n-octanol / water), Shake Flask Method)

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
Acetone 67-64-1	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Propane 74-98-6	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Butane, n- (< 0.1 % butadiene) 106-97-8	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Isobutane 75-28-5	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

Disposal must be made according to official regulations.

Waste code

14 06 03 Other solvents and solvent mixtures

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information**14.1. UN number**

ADR	1950
RID	1950
ADN	1950
IMDG	1950
IATA	1950

14.2. UN proper shipping name

ADR	AEROSOLS
RID	AEROSOLS
ADN	AEROSOLS
IMDG	AEROSOLS
IATA	Aerosols, flammable

14.3. Transport hazard class(es)

ADR	2.1
RID	2.1
ADN	2.1
IMDG	2.1
IATA	2.1

14.4. Packing group

ADR
RID
ADN
IMDG
IATA

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable Tunnelcode: (D)
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content 95 %
(2010/75/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H220 Extremely flammable gas.
- H225 Highly flammable liquid and vapor.
- H302 Harmful if swallowed.
- H312 Harmful in contact with skin.
- H319 Causes serious eye irritation.
- H332 Harmful if inhaled.
- H336 May cause drowsiness or dizziness.

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.