



### Main

Range	Acti 9
Product name	Disbo iC60
Product or component type	Miniature circuit-breaker
Device short name	IC60H
Poles description	3P
Number of protected poles	3
[In] rated current	1 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	70 KA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 70 KA Icu at 12...133 V AC 50/60 Hz conforming to EN/IEC 60947-2 70 KA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 50 KA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 10000 A Icn at 415 V AC 50/60 Hz conforming to EN/IEC 60898-1 20 KA Icu at 100...133 V DC conforming to EN/IEC 60947-2
Utilisation category	Category A conforming to EN/IEC 60947-2

### Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	440 V AC 50/60 Hz
Magnetic tripping limit	8 x In +/- 20 %
[Ics] rated service breaking capacity	70 KA 100 % conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz 70 KA 100 % conforming to EN/IEC 60947-2 - 12...133 V AC 50/60 Hz 70 KA 100 % conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 50 KA 100 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 7500 A 75 % conforming to EN/IEC 60898-1 - 415 V AC 50/60 Hz 20 KA 100 % conforming to EN/IEC 60947-2 - 100...133 V DC
Limitation class	3 conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 KV conforming to EN/IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	Trip indicator
Mounting mode	Clip-on
Mounting support	Rail
9 mm pitches	6
Height	85 Mm
Width	54 Mm

Depth	78.5 Mm
Net weight	0.375 Kg
Colour	White
Mechanical durability	20000 Cycles
Electrical durability	10000 Cycles
Provision for padlocking	Padlockable
Connections - terminals	Single terminal (top or bottom) 1...25 mm <sup>2</sup> rigid Single terminal (top or bottom) 1...16 mm <sup>2</sup> flexible
Wire stripping length	14 Mm for top or bottom connection
Tightening torque	2 N.M top or bottom
Earth-leakage protection	Separate block

## Environment

Standards	EN/IEC 60898-1 EN/IEC 60947-2
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Package 1 Weight	0.337 Kg
Package 1 Height	0.750 Dm
Package 1 width	0.540 Dm
Package 1 Length	0.900 Dm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**