

Type JX Thermocouple Wire Heat-Resistant PVC, 240V

multicomp PRO

**RoHS
Compliant**



Characteristics

Voltage Rating	: 240V
Temperature Range	: Rating - 105°C
Nominal Overall Diameter	: 2.85mm × 4.7mm Flatform Construction
Size / Strands	: 1 Pair, 7 strands/0.2mm
CSA	: 0.22mm ²
Core Identification	: Black and White Inner
Sheath	: Black

Cable Standards

EMF to BSEN60584-1 1996 (type JX) tolerances To BSEN60584-2 1993 class 2 @ 0-100°C IEC 584-3

Construction

Conductor	: Type JX (Iron/Constantan)
Insulation	: Heat Resistance PVC
Sheath	: Heat Resistance PVC

Note: Supplied in 100 metre reels or continuous length in 1 metre multiples.

Part Number Table

Description	Cable Length	Part Number
Type JX Thermocouple Wire, 1 Pair, Heat-Resistant PVC, Black	100m or per metre	PP002482

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO