multicomp PRO

RoHS

Compliant



Characteristics

Voltage Rating	: 240V
Temperature Range	: Rating - 400°C
Nominal Overall Diameter	: 1mm × 2mm Flatform Construction
Size / Strands	: 1 Pair, 1 solid/0.3mm
CSA	: 0.07mm ²
Core Identification	: Green and White Inner
Braided Sheath	: White with Green Stripes

Cable Standards

EMF to BSEN60584-1 1996 (type KX) tolerances To BSEN60584-2 1993 class 1 @ 0-300°C IEC 584-3

Construction

Conductor	: Type KX Chromel-Alumel (NiCr-NiAl)
Insulation	: Fibre Glass
Sheath	: Fibre Glass Braided

Note: Supplied in 50 metre reels or continuous length in 1 metre multiples.

Part Number Table

Description	Cable Length	Part Number
High Temperature Type KX Thermocouple Wire 1 Pair, Fibre Glass Braided Sheath	50m or per metre	PP002484

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

