

## START eco Flood Flat PIR


START eco Flood Flat IP54 PIR 2800lm 830

0047966



### Product features

- The new Start eco Flood Flat comes with improved design. The streamlined, durable, lightweight die-cast aluminium body makes it a perfect choice for building facades, car parks, garages and construction areas. The product includes 1 m pre-wired stripped cable and fitting bracket for quick and easy installation and the universal mounting bracket allows wall or surface mounting with the possibility of vertical tilting. Black die-cast aluminum housing, white reflector, 2700 lm, 31 W, 87 lm/W, 3000K, drive current 116 mA, non dimmable, CRI>80, IP54, IK06 - fixture, IK05 - sensor, Class I, lumen maintenance L70:B50: 30000 hrs, 156 x 178 x 67 mm (L x W x H). Weight: 0.61kg. PIR sensor included. Energy class: A++ A+ A.



### PRODUCT OVERVIEW

IPC Code	0047966
Product name	START eco Flood Flat IP54 PIR 2800lm 830
Technology	LED
Housing	Aluminium
General application	Residential & Consumer
Certifications	EUNEW005
ETIM Class	EC001744
E-number FI	4579428
Fixture luminous flux (lm)	2700
Luminaire efficacy (lm/W)	87
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Beam Angle (°)	110
Photobiological Risk Group	RG1
Total power consumption (W)	31
Electrical protection	Class I
Housing colour	RAL 9017 - Traffic black
IP rating	IP54
IK rating	IK05
Product EAN number	5410288479668
Lamps	No

### DATA TABLE

#### General data

IPC Code	0047966
Product name	START eco Flood Flat IP54 PIR 2800lm 830
Technology	LED
Housing	Aluminium
General application	Residential & Consumer
Operating temperature range (°C)	-20°C - 40°C
Certifications	EUNEW005

## START eco Flood Flat PIR

START eco Flood Flat IP54 PIR 2800lm 830

0047966

ETIM Class	EC001744
E-number FI	4579428

### Optical data

Fixture luminous flux (lm)	2700
Luminaire efficacy (lm/W)	87
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Beam Angle (°)	110
Photobiological Risk Group	RG1

### Electrical data

Total power consumption (W)	31
Mains voltage (V)	220-240V~
Lamp power factor	0.9
Electrical protection	Class I
Drive current (mA)	116
Inrush Current (A)	13.6
Inrush Duration (µs)	400
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	28
Max. Luminaires per 13A C Breaker	38
Max. Luminaires per 16A C Breaker	47
Max. Luminaires per 20A C Breaker	58
Max. Luminaires per 10A B Breaker	14
Max. Luminaires per 13A B Breaker	19
Max. Luminaires per 16A B Breaker	23
Max. Luminaires per 20A B Breaker	29

### Lifetime data

Lumen maintenance - L70 B50	30000
-----------------------------	-------

### Physical data

Housing colour	RAL 9017 - Traffic black
IP rating	IP54
IK rating	IK05
Nominal Product Length (mm)	156
Nominal Product Width (mm)	178
Nominal Product Height (mm)	67
Weight (kg)	0.61
Wind Area (m <sup>2</sup> )	0.038

### Packaging


Single packaging type	Carton
Product EAN number	5410288479668
Packaging single length / height (cm)	15.9
Packaging single width (cm)	9.4
Packaging single depth (cm)	19.0

## START eco Flood Flat PIR

START eco Flood Flat IP54 PIR 2800lm 830  
0047966

DUN14 (outer)	15410288479665
Units per outer package	8
Packaging outer length / height (cm)	40.0
Packaging outer width (cm)	33.7
Packaging outer depth (cm)	22.3


### PHOTOMETRY



Distance [m]	Cone diameter [m]	E(0°) E(C0)	Illuminance [lx]
0.5	1.47	3959 55.7°	355
1.0	2.93	990 55.7°	59
1.5	4.40	440 55.7°	39
2.0	5.86	247 55.7°	22
2.5	7.33	158 55.7°	14
3.0	8.80	110 55.7°	10

Distance [m] Cone diameter [m]  
C0 - C180 (Half beam angle: 111.4°) Illuminance [lx]


### TECHNICAL DRAWINGS




## START eco Flood Flat PIR


START eco Flood Flat IP54 PIR 2800lm 830  
0047966


**SYLVANIA** 0047966


 This luminaire contains built-in LED lamps

 } LED


The lamps cannot be changed in the luminaire.

874/2012 

 This luminaire contains built-in LED lamps

 } LED

The lamps cannot be changed in the luminaire.

**SYLVANIA** 0047966 

874/2012