

**Test Report**

No. 2045478/EC

Date : Jan 19 2006

Page 1 of 3

MULTICOMP PRODUCTS MANUFACTURED BY  
FREEPORT RESOURCES ENTERPRISES CORP  
Wusha the 6<sup>th</sup> Industrial Ave, Wu Sha Village,  
Chang-An Town, Dongguan City,  
Guangdong Province , China 523857

Report on the submitted sample said to be Strain Relief for Centronics IDC Ribbon connectors

SGS Job No. : 1931705  
Part Description : B505F\* Series  
Buyer : PREMIER FARNELL ASIA PTE. LTD.  
Supplier : FREEPORT RESOURCES ENTERPRISES CORP  
Sample Receiving Date : DEC 02 2005  
Testing Period : DEC 03 - 09 2005

Test Requested : With reference to RoHS Directive 2002/95/EC

- 1) To determine the Cadmium Content in the submitted sample.
- 2) To determine the Lead Content in the submitted sample.
- 3) To determine the Mercury Content in the submitted sample.
- 4) To determine the Hexavalent Chromium Content on the submitted sample.
- 5) Determination of PBBs (polybrominated biphenyls), PBDEs (Polybrominated diphenylethers) of the submitted sample.

Test Method : 1) With reference to BS EN 1122:2001, Method B, analysis was performed by Inductively Coupled Argon Plasma-Atomic Emission Spectrometry (ICP-AES).  
2) With reference to EPA Method 3050B/ 3051/ 3052. Analysis was performed by Inductively Coupled Argon Plasma-Atomic Emission Spectrometry (ICP-AES).  
3) With reference to EPA Method 3051/ 3052. Analysis was performed by Inductively Coupled Argon Plasma-Atomic Emission Spectrometry (ICP-AES).  
4) With reference to EPA Method 3060A & 7196A. The samples were alkaline digested by using EPA Method 3060A, and then analyzed by using Colorimetric method 7196A.  
5) With reference to EPA Method 3540C/ 3550C. Analysis was performed by GC/MS or LC/ MS.

Test Results : 1-5) Please refer to next page.

Conclusion : When tested as specified, the submitted sample complies with the requirements of Commission Decision of 18 Aug 2005 amending Directive 2002/95/EC notified under document 2005/618/EC.

Signed for and on behalf of  
SGS Hong Kong Ltd

Wan Chi Wai, Leo  
Technical Manager

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company.



# Test Report

No. 2045478/EC

Date : Jan 19 2006

Page 2 of 3

## Test Results :

1-4)

Test Item	Blue Plastic	Detection Limit	Limit
Cadmium (Cd)	ND	2 ppm	100 ppm
Lead (Pb)	ND	2 ppm	1000 ppm
Mercury (Hg)	ND	2 ppm	1000 ppm
Hexavalent Chromium (Cr <sup>6+</sup> )	ND	2 ppm	1000 ppm

(Results shown are of the total weight of samples)

Note : ppm = mg/kg

ND = Not Detected

Not detected is reported when the reading is less than detection limit value

5)

Flame Retardants	Blue Plastic	Detection Limit	Limit
<b>Polybrominated Biphenyls (Mono – Deca)</b>	ND	50 ppm	1000 ppm
Monobromobiphenyl	ND	5 ppm	--
Dibromobiphenyl	ND	5 ppm	--
Tribromobiphenyl	ND	5 ppm	--
Tetrabromobiphenyl	ND	5 ppm	--
Pentabromobiphenyl	ND	5 ppm	--
Hexabromobiphenyl	ND	5 ppm	--
Heptabromobiphenyl	ND	5 ppm	--
Octabromobiphenyl	ND	5 ppm	--
Nonabromobiphenyl	ND	5 ppm	--
Decabromobiphenyl	ND	5 ppm	--
<b>Polybrominated Diphenylethers (Mono – Nona)</b>	ND	45 ppm	1000 ppm
Monobromodiphenyl ether	ND	5 ppm	--
Dibromodiphenyl ether	ND	5 ppm	--
Tribromodiphenyl ether	ND	5 ppm	--
Tetrabromodiphenyl ether	ND	5 ppm	--
Pentabromodiphenyl ether	ND	5 ppm	--
Hexabromodiphenyl ether	ND	5 ppm	--
Heptabromodiphenyl ether	ND	5 ppm	--
Octabromodiphenyl ether	ND	5 ppm	--
Nonabromodiphenyl ether	ND	5 ppm	--
Decabromodiphenyl ether*	ND	5 ppm	See remark

Note : ppm = mg/kg

ND = Not Detected

Not detected is reported when the reading is less than detection limit value.

Remark: \* Decabromodiphenyl ether (DecaBDE) in polymeric applications is exempted by Commission Decision of 13 Oct 2005 amending Directive 2002/95/EC notified under document 2005/717/EC.


This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company.

**Test Report**

No. 2045478/EC

Date : Jan 19 2006

Page 3 of 3

**PHOTO APPENDIX**

SGS authenticate the photo on original report only

\*\*\* End of Report \*\*\*

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company.