

6W EU Wall Plug Adapter

9V DC, 0.66A

multicompPRO

**RoHS
Compliant**



Features

- European Fixed AC Head
- Level VI Efficiency
- CE Approved

Description

Class II 6 Watt AC/DC European plug-in power supplies provide 6 Watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications.

Specifications

Input Voltage Range	100V AC to 240V AC
Input Frequency Range	47Hz to 63Hz
Input Current Rated	0.2A Max
Output Voltage Rating	+9V
Output Current Range	0.66A
Output Min Current	0A
Output Connection Type	2.1mm × 5.5mm × 12mm Centre Positive –Straight
Total Output Regulation	8.55-9.45V
Line and Load Regulation	±2%
Ripple & Noise	300mVp-p
Efficiency	78.81% Min
Over Voltage Protection	Removal of an output overload shall provide automatic recover for the output voltage.
Over Load Protection	Removal of an output overload shall provide automatic recover for the output voltage.
Short-Circuit Protection	Auto Recovery
Operating Temperature	0°C to +40°C
Storage Temperature	-20°C to +70°C
Operating Humidity	10% to 95%
Storage Humidity	10% to 95%
Hi-Pot	3000Vac 4mA 1min
Safety Standard	EN60950-1:2006+A11+A1+A12+A2
MTBF	50K Hours
Size mm max.	61.6(L) × 26(W) × 76.5(H)
Weight	70g
Regulator Type	Switched Mode Power Supply

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicompPRO


6W EU Wall Plug Adapter

9V DC, 0.66A

multicompPRO

EMI Standard	EN55022:2010/AC:2011 EN61000-3-2:2014 EN61000-3-3:2013 EN55024:2010 IEC61000-4-2:2008 IEC61000-4-3:2006/A1:2007/A2:2010 IEC61000-4-4:2012 IEC61000-4-5:2014 IEC61000-4-6:2013 IEC61000-4-8:2009 IEC61000-4-11:2004
--------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Diagram



Dimensions : Millimetres

Part Number Table

Description	Part Number
Wall Plug Adapter, 6W, 9V DC, 0.66A, EU Plug	MP004762

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicompPRO