


3M™ Round Conductor Flat Cable

.033" 30 AWG Stranded, PVC

3849 Series



- 30 AWG stranded wire on .0333 inch centers permits termination to all three rows in DIN connectors.
- Stranded wire provides flexibility and extended product life.
- Zippable for branching or discrete termination
- RoHS* compliant

Date Modified: January 20, 2004

TS-0573-09
Sheet 1 of 2

Physical



Insulation

Material: Polyvinyl Chloride (PVC)

Color: Gray

Marking

Standard: None

CSA Option:  AWM 2651 105C 300V VW1 3M NU  AWM IA 105C 300V FT1
EU <50V

Conductors: 30 AWG 7 X 38 [7 X 0.102] Tinned Stranded Copper

Electrical

Voltage Rating:	USA: 300V	Canada: 300V	EU: <50V
Insulation Resistance:	> 1 X 10 ¹⁰ Ω/10 ft. [3m]		
	Unbalanced	Balanced	
Characteristic Impedance:	89 Ω	144 Ω	
Capacitance:	17.5 pF/ft. [57.4 pF/m]	10.5 pF/ft (34.5 pF/m)	
Inductance:	14 μH/ft. [0.46 μH/m]	.22 μH/ft (0.72 μH/m)	
Propagation Delay:	1.56 ns/ft. [5.12 ns/m]	1.51 ns/ft (4.95 ns/m)	
Velocity of Propagation:	65%	67%	

Note: Unbalanced is measured between ground-signal-ground conductors. Balanced is measured between signal conductors within a pair.

Environmental

Temperature Rating: -20°C to +105°C

Flammability Rating: USA: VW-1 Canada: FT1

*RoHS = Directive 2002/95/EC,
Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment

UL File No.: E42769, Style No.: 2651

3M
Interconnect Solutions
<http://www.3M.com/interconnects/>


3M is a trademark of 3M Company.
For technical, sales or ordering information call
800-225-5373

3M™ Round Conductor Flat Cable

.033" 30 AWG Stranded, PVC

3849 Series

Number of Conductors	3M Part Number	Dimension A	Dimension B
96	3849/96	3.197 ± .020 [81.20]	3.164 ± .015 [80.37]




Note: Red marking on one edge of cable designates wire #1.

	Inch [mm]		
	Tolerance Unless Noted		
	.0	.00	.000
Inch	±.1	± 01	±.005

[] Dimensions for Reference only

Ordering Information



Note: Standard length is 100 ft/roll.

TS-0573-09
Sheet 2 of 2

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.



Electronic Solutions Division

6801 River Place Blvd.
Austin, TX 78726-9000
www.3M.com/esd

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 1 year from the date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.**