

PRODUCT-DETAILS

## AE/S4.1.1.3

### AE/S4.1.1.3 Analogue Input, 4-fold, MDRC



#### General Information

Extended Product Type	AE/S4.1.1.3
Product ID	2CDG110190R0011
EAN	4016779929295
Catalog Description	AE/S4.1.1.3 Analogue Input, 4-fold, MDRC
Long Description	The analogue input is used to detect and process 4 independent input signals. E.g. 0-1 V, 0-5 V, 0-10 V, 0-20 mA, 4-20 mA, 0-1000 Ohm, PT100, PT1000 and floating contacts. Integrated power supply to generate the 24 V DC voltage for external sensors. The device can be operated with a supply voltage of 115 to 230 V, 50/60 Hz. Maximum 300 mA supplied on the complete voltage range. Application software adjusted for detection and processing of analogue variables.

#### Ordering

EAN	4016779929295
Customs Tariff Number	85389091
Minimum Order Quantity	1 piece
E-Number (Switzerland)	405631005
E-Number (Sweden)	1738904

#### Dimensions

Product Net Depth / Length	64.5 mm
Product Net Height	90 mm
Product Net Width	72 mm

Product Net Weight	0.23 kg
--------------------	---------

### Container Information

Package Level 1 Units	box 1 piece
Package Level 1 EAN	4016779929295
Package Level 1 Depth / Length	77 mm
Package Level 1 Height	65 mm
Package Level 1 Width	92 mm
Package Level 1 Gross Weight	0.27 kg

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	2CDC504084D0201
Instructions and Manuals	2CDG941143P0002
Declaration of Conformity - CE	2CDK504102D2701
RoHS Information	2CDK504102D2701

### Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

### Classifications

ETIM 5	EC000794 - Analogue input for bus system
ETIM 6	EC000794 - Analogue input for bus system
ETIM 7	EC000794 - Analogue input for bus system
eClass	7.0 27143107
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

### Categories

Low Voltage Products and Systems → Home and Building Automation → KNX → Standard Inputs → Analogue Inputs

