Straight BNC Jack-to-RCA Phono Plug Adaptor







Specifications

Electrical

Frequency Range : DC - 250 MHzNominal Impedance : BNC: 50Ω RCA: 75Ω

Material

Body : Brass, 100µ" Nickel Plated

Center Contact : Brass, Gold Plated


Insulation : POM

Washer : Brass, Nickel Plated

Environmental

Operating Temperature Range : -40°C to +60°C

Diagram



Dimensions: Millimetres (Inches)

No.	Description	Material	Finish	Qty.
1	Body	Brass	Nickel 100µ Min.	
2	Washer	Brass	Nickel	
3	Insulation	POM	None	1
4	Center Contact	Brass	Gold	
5	Insulation	POM	None	

Part Number Table

Description	Part Number	
Straight RCA Plug – BNC Jack Adaptor, $75\Omega/50\Omega$	MP-R14-005-01-000112000	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

