



CorePro LEDspot MV

CorePro LEDspot 4-35W GU10 827 36D DIM

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E27 base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance cost.

Product data


General Information		Temperature	
Cap-Base	GU10 [GU10]	Lamp Current (Nom)	25 mA
EU RoHS compliant	Yes	Wattage Equivalent	35 W
Nominal Lifetime (Nom)	15000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50000X	Warm Up Time to 60% Light (Nom)	0.5 s
Technical Type	4-35W	Power Factor (Nom)	0.7
Light Technical		Voltage (Nom)	220-240 V
Color Code	827 [CCT of 2700K]	Controls and Dimming	
Beam Angle (Nom)	36 °	Dimmable	Yes
Luminous Flux (Nom)	250 lm	Approval and Application	
Luminous Intensity (Nom)	500 cd	Energy Efficiency Label (EEL)	A+
Color Designation	Warm White (WW)	Suitable For Accent Lighting	Yes
Correlated Color Temperature (Nom)	2700 K	Energy Consumption kWh/1000 h	4 kWh
Luminous Efficacy (rated) (Nom)	62.00 lm/W	Product Data	
Color Consistency	<6	Full product code	871869672133900
Color Rendering Index (Nom)	80	Order product name	CorePro LEDspot 4-35W GU10 827 36D DIM
LLMF At End Of Nominal Lifetime (Nom)	70 %	EAN/UPC - Product	8718696721339
Luminous Flux in 90° Cone (Rated)	250 lm	Order code	929001218632
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power (Nom)	4 W		

CorePro LEDspot MV

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001218632

Net Weight (Piece)	0.036 kg
--------------------	----------



Dimensional drawing



GU10 230V 5W-50W 385lm 36D 4000K GU10 ND


Product	D	C
CorePro LEDspot 4-35W GU10 827 36D DIM	50 mm	53 mm

Photometric data



LEDspotMV 35W-50W GU10 827 36D D

LEDspotMV 35W-50W GU10 827 36D D



LEDspotMV GU10 MR16 827

CorePro LEDspot MV

