


C4AQ, Film, Metallized Polypropylene, Automotive DC Link, 6 uF, 5%, 1500 VDC, 70°C, Lead Spacing = 37.5mm



| General Information | |
|---------------------|--------------------------------------|
| Series: | C4AQ |
| Dielectric: | Metallized Polypropylene |
| Style: | Radial |
| RoHS: | Yes |
| Lead: | 4 Wire Leads |
| Qualifications: | AEC-Q200, IEC61071, EN61071, VDE0560 |
| AEC-Q200: | Yes |
| Miscellaneous: | Rth = 23 C/W. |

| Dimensions | |
|------------|------------------|
| L | 42mm +0.6/-0.7mm |
| H | 24mm +0.2/-0.7mm |
| T | 35mm +0.4/-0.7mm |
| S | 37.5mm +/-0.4mm |
| S1 | 20.3mm +/-0.4mm |
| LL | 6mm +0/-2mm |
| F | 1.2mm +/-0.05mm |

| Specifications | |
|------------------------|---|
| Capacitance: | 6 uF |
| Capacitance Tolerance: | 5% |
| Voltage DC: | 1500 VDC |
| Temperature Range: | -55/+105°C |
| Rated Temperature: | 70°C |
| Dissipation Factor: | 0.02% (10 kHz 25C) |
| Insulation Resistance: | 5 MOhms |
| Max dV/dt: | 21 V/us |
| Resistance: | 9.6 mOhms (10kHz 70C) |
| Ripple Current: | 7.8 Amps Irms (10kHz 70C), 127 Amps Ipk |
| Inductance: | 9 nH |

| Packaging Specifications | |
|--------------------------|-----------|
| Packaging: | Bulk, Box |
| Packaging Quantity: | 60 |